

# Laptop Power Adapter Cord, C14 to C5 Adapter - 7A/125V or 2.5A/250V, 18 AWG, 6 ft. (1.83 m), Black

MODEL NUMBER: P014-006



Laptop power cord adapter connects your notebook or laptop with a 3-slot C6 power inlet to an AC outlet.

## Features

**Laptop Power Adapter Cord Connects Notebook Computers to an AC Outlet** This C5 to C14 power cord is designed for connecting a notebook computer, laptop or other device with a three-slot C6 inlet to a UPS system, PDU or other C13 connector. The 6-ft. (1.83 m) length allows you flexibility in placing equipment with respect to the power outlet.

## Highlights

- Recommended for powering notebook computers and laptops with C6 inlets
- 6-ft. (1.83 m) length allows flexibility in placing devices in relationship to AC outlet
- Ideal replacement for a worn-out or missing laptop adapter power cable

## Applications

- Connect a laptop or notebook computer to a PDU up to 6-ft. (1.83 m) away in your workstation
- Extend an existing power connection up to 6-ft. (1.83 m) to more easily place a device or reach a power source
- Provide a high-quality replacement for a worn-out or missing laptop power cord

## Package Includes

- P014-006 Laptop Power Adapter Cord, C14 to C5 Adapter - 6-ft. (1.83 m), Black

## Specifications

| OVERVIEW                    |                            |
|-----------------------------|----------------------------|
| UPC Code                    | 037332098757               |
| Device Compatibility        | Laptop; Computer; UPS; PDU |
| Country/Region              | North America              |
| INPUT                       |                            |
| Maximum Input Amps          | 7                          |
| Voltage Compatibility (VAC) | 100-250                    |
| CONNECTIONS                 |                            |
| Side A - Connector 1        | IEC-320-C14                |
| Side B - Connector 1        | IEC-320-C5                 |
| PHYSICAL                    |                            |
| Plug Color                  | Black                      |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                      |                             |
|--------------------------------------|-----------------------------|
| Cable Jacket Color                   | Black                       |
| Cable Jacket Material                | PVC                         |
| Cable Jacket Rating                  | VW-1                        |
| Power Cord Jacket Type               | SJT                         |
| Cable Outer Diameter (OD)            | 7.8mm                       |
| Number of Conductors                 | 3                           |
| Wire Gauge (AWG)                     | 18                          |
| Wire Gauge (OD - mm <sup>2</sup> )   | 0.82                        |
| Cable Length (ft.)                   | 6                           |
| Cable Length (m)                     | 1.83                        |
| Shipping Dimensions (hwd / in.)      | 12.80 x 8.90 x 0.50         |
| Shipping Dimensions (hwd / cm)       | 32.51 x 22.61 x 1.27        |
| Shipping Weight (lbs.)               | 0.46                        |
| Shipping Weight (kg)                 | 0.21                        |
| Unit Dimensions (hwd / in.)          | 12.800 x 8.900 x 0.500      |
| <b>ENVIRONMENTAL</b>                 |                             |
| Operating Temperature Range          | -4° to 140°F (-20° to 60°C) |
| Storage Temperature Range            | -4° to 140°F (-20° to 60°C) |
| Operating Humidity Range             | 10% to 65% RH               |
| Storage Humidity Range               | 10% to 65% RH               |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                             |
| Antibacterial                        | No                          |
| Angled Plug                          | No                          |
| High Voltage                         | Yes                         |
| Locking Plug                         | No                          |
| Coiled Power Cord                    | No                          |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                             |
| Product Certifications               | cUL Listed; UL Listed       |
| Product Compliance                   | RoHS                        |
| <b>WARRANTY &amp; SUPPORT</b>        |                             |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty   |



*Powering Business Worldwide*

TRIPP LITE  
SERIES

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.