

Power Extension Cord, NEMA L5-30P to NEMA L5-30R- Heavy-Duty, 30A, 125V, 10 AWG, 10 ft. (3.05 m), Black, Locking Connectors

MODEL NUMBER: P046-010-LL-30A



Heavy-duty extension cord connects your computer or other device with a NEMA L5-30P plug to a NEMA L5-30R outlet.

Features

Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection This cord features 10 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It can be used to connect a computer, server or other device with a NEMA L5-30P plug to a wall outlet, PDU or UPS system with a NEMA L5-30R outlet. The six-foot length allows you flexibility in placing equipment with respect to the power outlet.

Locking Connectors Help Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. Locking connectors on each end help you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

Specifications

OVERVIEW	
UPC Code	037332200945
Device Compatibility	UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	30
Voltage Compatibility (VAC)	125

Highlights

- Recommended for powering computers, servers and other network devices
- 10-ft. (3.05 m) length allows flexibility in placing devices in relationship to AC outlet
- Heavy-duty cord replaces or upgrades standard power cord provided by manufacturer
- Thick 10 AWG wire gauge manages high power levels required for larger equipment
- Locking connectors maintain secure link to avoid loss of power and costly downtime

Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 10 ft. to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

Package Includes

- P046-006-LL-30A L5-30P to L5-30R Heavy-Duty Extension Cord, 10 ft., Black, Locking Connectors



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	NEMA L5-30P
Side B - Connector 1	NEMA L5-30R
PHYSICAL	
Plug Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	14.6mm
Number of Conductors	3
Wire Gauge (AWG)	10
Wire Gauge (OD - mm ²)	5.26
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (cm)	304.80
Shipping Dimensions (hwd / in.)	0.50 x 10.00 x 14.70
Shipping Dimensions (hwd / cm)	1.27 x 25.40 x 37.34
Shipping Weight (lbs.)	2.60
Shipping Weight (kg)	1.18
Unit Dimensions (hwd / in.)	0.500 x 10.000 x 14.700
Unit Weight (lbs.)	2.6000
Unit Weight (kg)	1.18
ENVIRONMENTAL	
Operating Temperature Range	14° to 140°F (-10° to 60°C)
Storage Temperature Range	14° to 140°F (-10° to 60°C)
Operating Humidity Range	35% to 85% RH, Non-Condensing
Storage Humidity Range	35% to 85% RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Antibacterial	No
Angled Plug	No
High Voltage	No
Locking Plug	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Coiled Power Cord	No
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.