

Important Note

The P130-000-COMP is intended for applications such as viewing video content with audio. For standard computer usage, desktop icons and other text may appear less sharp than if a direct cable connection is used.

HDMI to RCA Composite Video Adapter with Audio (F/3xF)

MODEL NUMBER: P130-000-COMP



Convert an HDMI audio/video signal for use with an analog TV or monitor equipped with RCA composite video and audio ports.

Features

Convert HDMI to Composite Video and Audio for Compatibility with Analog Displays

This P130-000-COMP converter connects an HDMI source, such as a laptop or Blu-ray player, to a television, monitor or projector equipped with RCA composite audio/video connectors. A switch allows you to select either the NTSC or PAL video standard for compatibility with a wide range of devices. The converter has a female HDMI input and female RCA composite video (yellow) and stereo audio (red and white) outputs (cables sold separately).

Save Money without Sacrificing Image and Sound Quality

This HDMI to composite video and audio converter helps you save money by making your current composite video television or monitor compatible with an HDMI-equipped video source, eliminating the need to purchase a new HDMI display. It is HDCP-compliant and supports HDMI input video resolutions of 480i, 480p, 576i, 576p, 720p, 1080i and 1080p (50/60 Hz). The converter supports output video resolutions up to 480i (NTSC) and 576i (PAL). It also supports uncompressed two-channel (right/left) stereo audio.

Simplify Installation with a Versatile Plug-and-Play Solution

This plug-and-play converter requires no software or drivers. Just connect your devices and plug in the included 100-240V power supply. Suitable for use in many countries, the power supply comes with four plug adapters: NEMA 1-15P (North America), CEE 7/16 Schuko (Europe), BS1363 (United Kingdom) and AS/NZS 3112 (Australia).

Highlights

- Allows an HDMI video source to work with RCA A/V ports
- Converts high-quality HDMI video up to 1080p
- Supports both NTSC (up to 480i) and PAL (up to 576i) video standards
- 100-240V power supply and plug adapters offer wide compatibility
- Plug-and-play operation with no software required for easy, immediate installation

System Requirements

- Video source with HDMI output
- Display with RCA composite video and stereo audio inputs

Package Includes

- P130-000-COMP HDMI to Composite Video with Audio Converter (F/3xF)
- External power supply (Input: 100-240V, 50/60 Hz, 0.3A; Output: 5V 1A) with 5 ft. cord
- (4) Plug adapters (North America, Europe, United Kingdom and Australia)
- Mounting hardware
- Owner's manual

Specifications

OVERVIEW



Powering Business Worldwide

TRIPP LITE
SERIES

UPC Code	037332192738
Product Type	Video Adapter
Technology	Composite; HDMI; Stereo Audio
CONNECTIONS	
Side A - Connector 1	HDMI (FEMALE)
Side B - Connector 1	RCA (FEMALE)
PHYSICAL	
Color	Black
Cable Length (ft.)	0
Cable Length (m)	0.00
Shipping Dimensions (hwd / in.)	2.00 x 7.40 x 8.50
Shipping Dimensions (hwd / cm)	5.08 x 18.80 x 21.59
Shipping Weight (lbs.)	1.20
Shipping Weight (kg)	0.54
Unit Dimensions (hwd / in.)	0.000 x 0.000 x 0.000
Unit Weight (lbs.)	1.36
Unit Weight (kg)	0.62
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	2-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.