

DisplayPort to DVI Active Adapter Video Converter, DP ver 1.2, (M/F), 6-in. (15.24 cm)

MODEL NUMBER: **P134-06N-DVI-V2**



Converts a DisplayPort 1.2 video signal for display on a DVI monitor, projector or television.

Features

Send High-Definition DisplayPort 1.2 Video Signals to a DVI Display

- Connects DisplayPort 1.2 computer to DVI-enabled monitor, projector or TV
- Ideal for displaying video on large monitor or digital sign
- Female DVI-I dual-link and male DisplayPort connectors
- Backward compatible with previous DisplayPort generations

Vibrant, Superior Video Quality

- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts both Single-Mode and Dual-Mode DisplayPort output
- Works with graphics cards that don't output DP++ signals, such as AMD Eyefinity

Superior Materials for Superior Performance

- Gold-plated connectors and contacts for excellent conductivity
- Integral strain relief for long life
- Plug-and-play—no software, drivers or power supply necessary
- Fits easily into briefcase, backpack or laptop bag

Specifications

OVERVIEW	
UPC Code	037332192035
Product Type	Video Adapter
Technology	DVI; DisplayPort

Highlights

- Active converter works with all DisplayPorts
- Supports HD video resolutions up to 1920 x 1080 (1080p)
- Converts both Single-Mode and Dual-Mode DisplayPort output
- Plug and play—no software, drivers or power supply needed
- Gold-plated connectors and contacts

Package Includes

- P134-06N-DVI-V2 DisplayPort 1.2 to DVI Active Converter (M/F), 6 in.



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	DVI-I DUAL-LINK (FEMALE) (WIRED TO DVI-D SINGLE-LINK)
PHYSICAL	
Color	Black
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	7.00 x 9.00 x 0.50
Shipping Dimensions (hwd / cm)	17.78 x 22.86 x 1.27
Shipping Weight (lbs.)	0.09
Shipping Weight (kg)	0.04
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.