

Keyspan Mini DisplayPort to HDMI Active Adapter/Video Converter (M/F) - 4K 60 Hz, DP 1.2, HDCP 2.2, Black, 6 in.

MODEL NUMBER: P137-06N-HD4K6B



Mini DisplayPort to HDMI adapter connects a 4K HDMI display to the mDP or Thunderbolt 1/2 output on your computer.

Features

Mini DisplayPort to HDMI Adapter Connects Your mDP Laptop to a 4K HDMI Display

This Keyspan® active Mini DisplayPort 1.2 to HDMI adapter connects an HDMI monitor, projector or television to the Mini DisplayPort or Thunderbolt 1 or 2 port on your PC, Mac, Chromebook, MacBook, Microsoft Surface or other compatible computer or tablet. It features male mDP and female HDMI connectors, so you can continue using your existing HDMI display and cable to transmit audio/video without the expense of a new mDP display (check your source device's manual for audio compatibility).

Transmits Crystal-Clear Video up to 4K x 2K for Ultra HD Presentations

Ideal for video presentations and home/office applications, this Mini DisplayPort to HDMI adapter supports Ultra High Definition (UHD) video resolutions up to 4K at 60 Hz (3840 x 2160) as specified in HDMI 2.0. The active adapter converts both single-mode and dual-mode (DP++) DisplayPort output. It's recommended for use with graphics cards, such as AMD Eyefinity, that do not output DP++ signals. The HDMI port is backward compatible with non-4K displays.

Ready to Use Right from the Package, So You Can Plug and Play Immediately

The plug-and-play active Mini DisplayPort to HDMI adapter requires no software, drivers or external power, works with both Windows and Mac operating systems, and is compatible with laptops, tablets and other devices equipped with a female Mini DisplayPort or Thunderbolt 1 or 2 port. With its small size, the P137-06N-HD4K6B is recommended for stowing in your laptop bag and carrying to school, the office or the latest trade show.

Highlights

- Continue using your current HDMI display with your Mini DisplayPort or Thunderbolt computer
- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Also converts mDP audio to HDMI for complete audio/video transmission
- Compact unit fits easily into briefcase or laptop bag for instant use anywhere
- Plug-and-play operation with no software required for easy, immediate installation

Applications

- Transmit audio and 4K video to an existing HDMI monitor without the expense of buying a new Mini DisplayPort monitor
- Extend your laptop's display to a secondary HDMI monitor
- Give a 4K video presentation in a classroom, conference room or at the office

System Requirements

- Source device with Mini DisplayPort, Thunderbolt 1 or Thunderbolt 2 output
- Display device with HDMI input
- HDMI cabling
- Both source and display must support 4K @ 60 Hz to transmit 4K x 2K video signals

Package Includes

P137-06N-HD4K6B Keyspan Mini DisplayPort 1.2 to HDMI Active Adapter, Black, 6 in.

Specifications

OVERVIEW	
UPC Code	037332210616
Product Type	Video Adapter
Technology	HDMI; DisplayPort



Powering Business Worldwide

TRIPP LITE
SERIES

INPUT	
Product Length (in.)	6
CONNECTIONS	
Side A - Connector 1	MINI DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
PHYSICAL	
Color	Black
Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.06
Shipping Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10 to 85%, RH, Non-Condensing
Storage Humidity Range	5 to 90%, RH, Non-Condensing
FEATURES & SPECIFICATIONS	
Displayport Specification	1.2
HDCP Specification	2.2
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.