

## PS/2 Keyboard or Mouse Extension Cable (Mini-DIN6 M/F), 50 ft. (15.24 m)

MODEL NUMBER: P222-050



### Highlights

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- PS/2 Keyboard or Mouse Extension, 50ft

### System Requirements

- PS/2 device or cable with MiniDin6 Male connector

### Package Includes

50-ft. (15.24 m) PS/2 Keyboard/Mouse Extension MiniDIN6M to MiniDIN6F

### Description

Extend the length of the cable on any PS/2 device, such as a mouse or keyboard, by using a 50-foot (15.2-meter) PS/2 extension cable. MiniDIN6 male to MiniDIN6 female. Superior molded cables with foil-shielding for maximum EMI/RFI protection.

### Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- For PS/2 keyboards and mice
- MiniDIN6 (male) to MiniDIN6 (female), 50-ft. (15.24 m)

## Specifications

| OVERVIEW             |                     |
|----------------------|---------------------|
| UPC Code             | 037332147226        |
| Technology           | PS/2                |
| CONNECTIONS          |                     |
| Side A - Connector 1 | MINI DIN-6 (MALE)   |
| Side B - Connector 1 | MINI DIN-6 (FEMALE) |
| PHYSICAL             |                     |
| Color                | Beige               |
| Cable Jacket Color   | Beige               |
| Cable Length (ft.)   | 50                  |



Powering Business Worldwide

TRIPP LITE  
SERIES

|                                     |                           |
|-------------------------------------|---------------------------|
| Cable Length (m)                    | 15.24                     |
| Shipping Dimensions (hwd / in.)     | 1.00 x 5.60 x 5.80        |
| Shipping Dimensions (hwd / cm)      | 2.54 x 14.22 x 14.73      |
| Shipping Weight (lbs.)              | 0.70                      |
| Shipping Weight (kg)                | 0.32                      |
| <b>STANDARDS &amp; COMPLIANCE</b>   |                           |
| Product Compliance                  | RoHS                      |
| <b>WARRANTY &amp; SUPPORT</b>       |                           |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.