

DisplayPort to HDMI Active Adapter Video Converter (M/F), 4K 60 Hz, DP 1.2, HDCP 2.2, 6 in.

MODEL NUMBER: P136-06N-H2V2



Converts DisplayPort 1.2 audio and 4K x 2K video for display on an HDMI monitor, projector or television.

Features

Sends DisplayPort 1.2 Audio/Video to an HDMI Display Connects DisplayPort 1.2 computer to HDMI-enabled monitor, projector or TV. Ideal for displaying video on large monitor or digital sign. Female HDMI and male DisplayPort connectors.

Vibrant Video Quality Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160) as specified in HDMI 2.0. Supports audio and HDCP 2.2. Compatible with both Single-Mode and Dual-Mode DisplayPort output. Works with graphics cards that don't output DP++ signals.

Superior Materials for Superior Performance Molded connectors with corrosion-resistant gold-plated contacts for excellent conductivity. Integral strain relief for long life. Plug-and-play—no software, drivers or power supply necessary. Fits easily into briefcase, backpack or laptop bag.

Specifications

OVERVIEW	
UPC Code	037332200334
Product Type	Video Adapter
Technology	HDMI; DisplayPort
CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (FEMALE)
PHYSICAL	
Color	Black

Highlights

- Supports UHD resolutions up to 4K @ 60 Hz for crystal-clear video
- Supports audio and HDCP 2.2
- Compatible with Single-Mode and Dual-Mode DisplayPort output
- Plug-and-play operation with no software required for easy, immediate installation

Package Includes

- P136-06N-H2V2 DisplayPort 1.2 to HDMI Active Converter (M/F), 6 in.



Powering Business Worldwide

TRIPP LITE
SERIES

Cable Length (ft.)	0.5
Cable Length (m)	0.15
Cable Length (in.)	6
Cable Length (cm)	15.24
Shipping Dimensions (hwd / in.)	9.00 x 7.20 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 18.29 x 1.27
Shipping Weight (lbs.)	0.10
Shipping Weight (kg)	0.05
STANDARDS & COMPLIANCE	
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.