

## USB-C to HDMI Adapter with PD Charging, HDCP, White

MODEL NUMBER: U444-06N-H4-C



USB 3.2 Gen 1 to HDMI adapter adds HDMI and USB-C PD ports to your laptop, MacBook or other compatible device.

### Features

**USB-C to HDMI Adapter Connects to Your Device's USB-C or Thunderbolt 3 Port** This USB 3.2 Gen 1 to HDMI adapter helps you transmit video from your tablet, laptop, Chromebook, MacBook, smartphone or PC to an HDMI-enabled television, monitor or projector. It's ideal for transmitting digital audio and 4K video to a large display, as well as powering and charging a PD Charging-compliant mobile device. **Supports USB DisplayPort 1.2 Alternate Mode for Transmitting Video Signals**

With a source device that also supports USB DisplayPort Alt Mode, you can extend video from your primary display to another, duplicate the same video on both displays, or change the second display to your primary.

**Transmits Crystal-Clear 4K HDMI Video and Digital Audio** To send digital audio and Ultra High Definition video to a 4K-ready HDMI television, projector or monitor, connect the HDMI port to the display using an HDMI cable (sold separately). The HDMI port supports UHD video resolutions up to 3840 x 2160 (4K) at 30 Hz. The adapter is backward compatible with non-4K displays.

**Charges the Connected Laptop, Smartphone or Other Device** The USB-C Power Delivery (PD) port provides power and charging to the PD Charging-compliant device (such as a MacBook, Chromebook or Android smartphone) the adapter is connected to. Connect the device's AC wall charger to the adapter's USB-C PD port, which supports power input up to 20V/3A (60W). **Note:** USB-C PD port does not support Quick Charge (QC).

**Built-In USB-C Cable Connects in Either Direction** Connect the reversible USB-C plug to your source device's USB-C or Thunderbolt 3 port. The fumble-free USB-C plug connects in either direction to ensure fast, easy connection every time.

**Ready to Use Right Out of the Package** The plug-and-play USB 3.2 to HDMI adapter requires no software, drivers or external power. It's smaller than a credit card, making it easy to carry in a pocket, briefcase or laptop bag for connecting on the go.

**3-Year Warranty and Environmentally Responsible Design** The U444-06N-H4-C comes with a 3-year warranty. It's manufactured in compliance with strict RoHS specifications, reflecting commitment to environmental responsibility.

### Highlights

- Transmits video signals from sources supporting USB DisplayPort Alt Mode
- Supports UHD video resolutions up to 3840 x 2160 (4K x 2K) @ 30 Hz
- Supports USB 3.2 Gen 1 speeds up to 5 Gbps to ensure fast data transfers
- USB-C PD charging port supports power input up to 20V 3A (60W)
- Plug-and-play operation with no software or drivers required

### Applications

- Watch 4K video content from a Blu-ray player, game console, laptop or tablet on an Ultra HD television or projector
- Connect a Chromebook or MacBook to a conference table's A/V box to give a video presentation on a large screen
- Charge and power a USB-C or Thunderbolt 3 device with its AC wall charger
- Connect a USB peripheral, such as an external hard drive, printer or hub

### System Requirements

- Source device with USB-C or Thunderbolt 3 port that supports USB DisplayPort Alternate Mode
- Display device with HDMI input (HDMI port)

### Package Includes

- U444-06N-H4-C USB 3.2 Gen 1 USB-C to HDMI 4K Adapter
- Owner's manual



Powering Business Worldwide

TRIPP LITE  
SERIES

## Specifications

OVERVIEW	
UPC Code	037332193926
Product Type	USB-C Multiport Adapter
Technology	HDMI
Host Connector	USB C (MALE)
VIDEO	
Video Input	USB C (MALE)
Video Output	HDMI (FEMALE)
Number of Monitors Supported	1
Video Ports	HDMI (FEMALE)
Video Ports Details	HDMI 1.4; HDCP 1.4; DisplayPort 1.2
Supported Resolutions	1280x720 (720p); 1920x1080 (1080p); 3840x2160 (4K)
Max Supported Video Resolution	3840 x 2160 (4K x 2K) @ 30Hz
Extended Mode	Yes
Mirror Mode	Yes
3D Video Supported	Yes
DisplayPort Alt Mode	Yes
INPUT	
Bus Powered	Yes
BATTERY	
Battery Charging (5V/1.5A Port)	No
POWER	
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	20V/3A; 60W
CONNECTIONS	
Side A - Connector 1	USB C (MALE)
Side B - Connector 1	HDMI (FEMALE)
Connector Plating	Nickel



Powering Business Worldwide

TRIPP LITE  
SERIES

CHARGING	
Number of Charging Ports	1
Total Charging Amps	3
Total Charging Watts	60
Charging Port Type	USB C (FEMALE)
Charging Ports	USB-C: 60W (20V 3A) Power Delivery (PD 2.0)
Charging Ports Details	Provides up to 60W (20V/3A) of power to the host device via the PD Charging port
Charging Ports / Amps	3A
PHYSICAL	
Color	White
Material of Construction	PVC, ABS
Cable Jacket Color	White
Cable Jacket Material	PVC
Cable Outer Diameter (OD)	3.9mm
Wire Gauge (AWG)	34 / 28
Number of Displays	1
Shipping Dimensions (hwd / in.)	0.80 x 3.90 x 4.70
Shipping Dimensions (hwd / cm)	2.03 x 9.91 x 11.94
Shipping Weight (lbs.)	0.20
Shipping Weight (kg)	0.09
Unit Dimensions (hwd / in.)	0.450 x 1.700 x 1.570
Unit Packaging Type	Box
Unit Weight (lbs.)	0.06
Unit Weight (kg)	0.03
ENVIRONMENTAL	
Operating Temperature Range	32° to 113°F (0° to 45°C)
Storage Temperature Range	14° to 158°F (-10° to 70°C)
Operating Humidity Range	10% to 85% RH, Non-Condensing
Storage Humidity Range	5% to 90% RH, Non- Condensing
FEATURES & SPECIFICATIONS	
USB Hub Ports	No
Number of USB Hub Ports	0
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps); USB 3.2 Gen 1 (up to 5 Gbps)



Powering Business Worldwide

TRIPP LITE  
SERIES

HDCP Specification	1.4
Driver Required	No
STANDARDS & COMPLIANCE	
TAA Compliant Option	N
Product Compliance	RoHS; CE (Europe); REACH; FCC (USA)
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.