

1-Port USB Wall/Travel Charger - USB-C 30W PD Charging, 3W Apple Watch Charging Pad, MFi, 1-15P Direct Plug-In, White

MODEL NUMBER: U280MS-2N1-WH2



Travel charger with PD charging powers your smartphone, tablet or Apple Watch in a hotel or airport.

Features

1-Port USB Charger with Magnetic Charging Pad Keeps Your Devices Powered and Ready

Ideal for travel use in a hotel, airport, coffee shop or library, as well as your home, office, retail or industrial workstation, this Apple MFi-certified two-in-one charger keeps a wide range of mobile devices charged and powered. The USB-C Power Delivery (PD) port features 30W for charging an iPhone, iPad or other smartphone or tablet with the appropriate cabling (sold separately). The U280MS-2N1-WH2's folding NEMA 1-15P plug connects directly to an available AC outlet, avoiding unnecessary cord clutter. **Note:** The charger is intended to be used with smartphones, tablets, handheld gaming consoles and other devices that require 30W of power or less. Attempting to charge a laptop or other device that typically demands greater than 30W of power can result in reduced charging output and overheating of the charger.

Supports Apple MagSafe Technology for a Secure Charge Every Time

Built-in MagSafe technology helps ensure your Apple Watch and the U280MS-2N1-WH2 work together for a complete charge whenever you need it. Magnets inside both your watch and the charging pad prevent the watch from falling off the charger and being disconnected while charging. The U280MS-2N1-WH2 delivers up to 3W of power to your Apple Watch or other compatible smartwatch.

Highlights

- Plugs directly into the wall (no cord required) for easy installation and less cable clutter
- USB-C charging port supports PD charging and PPS charging up to 30W
- MagSafe wireless magnetic charging pad charges Apple Watch up to 3W
- Features overcurrent, overload, overvoltage and short circuit protection
- Compact charger with folding NEMA 1-15P prongs designed for travel use

System Requirements

- Works with all MagSafe-compatible smartwatches, including Apple Watch
- USB-C port is intended for use with smartphones and tablets, including iPhones and iPads

Package Includes

- U280MS-2N1-WH2 30W USB Wall/Travel Charger
- Quick Start Guide

Specifications

OVERVIEW	
UPC Code	037332288189
Charging Form Factor	Direct Plug-In
Product Type	USB Charger; Wall Charger; Wireless Charger
Device Compatibility	Amazon Kindle; Phone; Tablet; Video Game System; Watch
Technology	USB
Country/Region	North America



Powering Business Worldwide

TRIPP LITE
SERIES

Host Connector	USB C (FEMALE)
INPUT	
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 12V DC; 140V AC; 200V AC; 208V AC; 220V AC; 230V AC; 240V AC
Maximum Input Amps	1
Input Connection Type	NEMA 1-15P
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240
Input Frequency	50/60 Hz
Input Plug Type	NEMA 1-15P
Input Current	100-240V, 0.85A (Max)
Bus Powered	No
Power Source	AC Adapter; USB
OUTPUT	
Output Capacity (Watts)	30
Continuous Output Capacity (Watts)	30
Overload Protection	Yes
POWER	
Power Source Type	AC Adapter
Power Source	Unit (Included)
Power Consumption (Watts)	30.00
USB Power Delivery (PD) Charging Support	Yes
USB Power Delivery (PD) Charging Specification	30W
CONNECTIONS	
Number of Ports	1
Side A - Connector 1	(1) NEMA 1-15P (NON-POLARIZED)
Side B - Connector 1	USB C (FEMALE)
Side B - Connector 2	WIRELESS CHARGING COIL
USER INTERFACE, ALERTS & CONTROLS	
LED Indicators	N/A
CHARGING	
Number of Charging Ports	2
Total Charging Amps	3



Powering Business Worldwide

TRIPP LITE
SERIES

Total Charging Watts	30
Charging Method	Magnetic Charger; USB; Wireless
Charging Method Detail	(x1) Wireless magnetic charging strip supports up to 3 Watts of charging power for magnetic charging-enabled devices(x1) USB-C port supports up to 30 Watts of charging power for USB-enabled devices
Charging Port Type	(1) USB C (FEMALE); (1) WIRELESS CHARGING COIL
Charging Ports Details	(x1) USB-C female charging port provides up to 30W PD Charging or PPS Charging to Apple, Samsung or other smartphones and tablets in the following outputs: PD Charging: 5V/3A (15W), 9V/3A (27W), 12V/2.5A (30W), 15V/2A (30W), 20V/1.5A (30W)PPS Charging: 5-11V/3A (30W Max)(x1) MagSafe charging pad provides up to 3W to Apple Watch or other compatible smart watches
Magnetic Charging	Yes
Wireless Charging	Yes
Overcharge Protection	Yes
Compatible Devices	Smartphone; Tablet; Video Game Console
PHYSICAL	
Color	White
Material of Construction	PC (PLASTIC), PC945 UL94V-0
Cable Jacket Color	White
Connector Color	White
Charging Station Form Factor	Direct Plug-In
Total Number of Ports	2
Unit Dimensions (hwd / in.)	2.130 x 1.540 x 1.610
Unit Dimensions (hwd / cm)	4.17 x 5.4 x 3.9
Unit Dimensions (hwd / mm)	41.7 x 54 x 39
Unit Packaging Type	Box
Unit Weight (lbs.)	0.11
Unit Weight (kg)	0.05
ENVIRONMENTAL	
Operating Temperature Range	32° to 77°F (0° to 25°C)
Storage Temperature Range	-4° to 140°F (-20° to 60°C)
Operating Humidity Range	20% to 90% RH (NON-CONDENSING)
Storage Humidity Range	5% to 95% RH (NON-CONDENSING)
FEATURES & SPECIFICATIONS	
GaN Technology	No
Overcurrent Protection	Yes
Overvoltage Protection	Yes
Over Current Protection	Yes



Powering Business Worldwide

TRIPP LITE
SERIES

Driver Required	No
Qi Compliant	Yes
Over Temperature Protection	Yes
STANDARDS & COMPLIANCE	
Product Certifications	CAN/CSA-C22.2 No. 62368-1 (Canada); UL 62368-1
Product Compliance	FCC (USA); FCC Part 15 Class B (USA); WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	1-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.