



Quality Products. Service Excellence.

Mounting Rack Rails *H1R Series*

For use with the H1, RCK, HWF, and NWC Cabinet Series



Features

- Rails are sold in pairs.
- Rails come numbered in 1U (1.75") increments.
- Installs vertically in the cabinet.
- Use with **H1**, **RCK**, **NWC**, and **HWF** Cabinet series.
- Includes **strut mounting hardware** (for both rails).
- Rails are compatible with 19" rack mounting.
- Finished in textured RAL9005 black powder paint finish.
- TAA-compliant for GSA Schedule purchases.
- RoHS Compliant.
- Manufactured in North America within an ISO 9001:2015 certified facility.



10-32 Threaded Rail Features

- Constructed in 12-gauge steel.
- EIA-compliant threaded 10-32 holes.

Square Hole Punched Rail Features

- Constructed in 12-gauge steel.
- EIA-compliant square hole punched.



19" Mounting Rails for 24" Wide Cabinets

Part No. Threaded 10-32	Part No. Square Hole	Usable Mounting Dimensions		Overall Cabinet
		Rack Units	Height	Width
H1TRR12U24BK	H1SRR12U24BK	12U	21.00	24.00
H1TRR18U24BK	H1SRR18U24BK	18U	31.50	24.00
H1TRR20U24BK	H1SRR20U24BK	20U	35.00	24.00
H1TRR24U24BK	H1SRR24U24BK	24U	42.00	24.00
H1TRR36U24BK	H1SRR36U24BK	36U	63.00	24.00
H1TRR42U24BK	H1SRR42U24BK	42U	73.50	24.00
H1TRR45U24BK	H1SRR45U24BK	45U	78.75	24.00
H1TRR48U24BK	H1SRR48U24BK	48U	84.00	24.00
H1TRR52U24BK	H1SRR52U24BK	52U	91.00	24.00

19" Mounting Rails for 30" Wide Cabinets

Part No. Threaded 10-32	Part No. Square Hole	Usable Mounting Dimensions		Overall Cabinet
		Rack Units	Height	Width
H1TRR36U30BK	H1SRR36U30BK	36U	63.00	30.00
H1TRR42U30BK	H1SRR42U30BK	42U	73.50	30.00
H1TRR45U30BK	H1SRR45U30BK	45U	78.75	30.00
H1TRR48U30BK	H1SRR48U30BK	48U	84.00	30.00
H1TRR52U30BK	H1SRR52U30BK	52U	91.00	30.00

19" Mounting Rails for 31.5" Wide Cabinets

Part No. Threaded 10-32	Part No. Square Hole	Usable Mounting Dimensions		Overall Cabinet
		Rack Units	Height	Width
H1TRR42U31BK	H1SRR42U31BK	42U	73.50	31.50
H1TRR45U31BK	H1SRR45U31BK	45U	78.75	31.50
H1TRR48U31BK	H1SRR48U31BK	48U	84.00	31.50
H1TRR52U31BK	H1SRR52U31BK	52U	91.00	31.50

Data subject to change without notice

© 2025. Hammond Manufacturing Ltd. All rights reserved.