




Atmel AVR UC3C 32-bit Flash Microcontrollers

Industrial and Automotive Control



Atmel® AVR® UC3C 32-bit Flash microcontrollers are designed for industrial and automotive control applications, including fast communication and motor control. The devices feature single or dual CAN interfaces, Full Speed USB with OTG, NAND Flash and SDRAM interface, PWM with dead-time insertion, 1.5 Msps 12-bit ADC with 8 channels and dual sample-and-hold circuit for synchronized sampling of 2 signals, and 1.5 Msps 12-bit analog DAC with dual outputs. Designed with a multi-layered databus, 68KB on-chip SRAM with triple high-speed interfaces, and multi-channel peripheral and memory-to-memory DMA controller, the AVR UC3C offers outstanding data throughput.

The AVR UC3C Event System provides a connection between on-chip peripherals to off-load the CPU, save power consumption and provide a 100% deterministic response to external and internal events.

The AVR UC3 delivers high computational throughput, deterministic real-time control, low power, low system cost, high reliability and ease of use. The CPU includes cutting-edge features such as DSP arithmetic, single-cycle multiply and accumulate instructions and single-cycle SRAM access. In addition, a peripheral DMA controller and multi-layer high-speed bus architecture make the UC3 core ideal for high throughput applications.

Key Features

- 64-512KB Flash
- 68KB SRAM (2 x 32KB + 4KB)
- Event System
- Single/Dual CAN interface
- Full Speed USB device + OTG
- SRAM/SDRAM controller
- NAND Flash controller
- 8 ch 12-bit ADC, 1.5 Msps with dual sample-and-hold
- 2 ch 12-bit DAC, 1.5 Msps
- PWM with dead-time insertion
- Memory-to-memory DMA
- High number of serial communication modules
- 144, 100 and 64-pin package options
- Available in QFP, QFN, and BGA package options

Advantages

- High data throughput
- High computing efficiency including DSP instructions
- Industry-best low power consumption
- Excellent real-time performance
- Free application source code

Sales Collateral

- AVR UC3 Sales Introduction
- AVR UC3 Technical Introduction
- AVR UC3 C Introduction
- Application Notes
- Datasheet

Example Applications

- Industrial control
- HVAC
- Home appliances
- Automotive

Product Status

All part numbers are in mass production and samples are available



Atmel AVR UC3C 32-bit Flash Microcontrollers

Industrial and Automotive Control

Development Tools

Kit P/N		
ATUC3C-EK	Evaluation kit	
AVR ONE!/ JTAGICE3	Debuggers	
Atmel Studio 6	IDE	
Atmel Software Framework	Library of C source code	
ATSTK600 + TQFP144	Starter kit	

Suggested Resale Price

Ordering Code	10KU
AT32UC3C064C-ALUT	\$4.86
AT32UC3C0128C-ALUT	\$5.87
AT32UC3C0256C-ALUT	\$7.21
AT32UC3C0512C-ALUT	\$8.51
AT32UC3C164C-AUT	\$4.53
AT32UC3C1128C-AUT	\$5.48
AT32UC3C1256C-AUT	\$6.73
AT32UC3C1512C-AUT	\$7.94
AT32UC3C264C-A2UT	\$4.21
AT32UC3C2128C-A2UT	\$5.09
AT32UC3C2256C-A2UT	\$6.25
AT32UC3C2512C-A2UT	\$7.38



Atmel Corporation 1600 Technology Drive, San Jose, CA 95110 USA **T:** (+1)(408) 441-0311 **F:** (+1)(408) 487-2600 | **www.atmel.com**

© 2012 Atmel Corporation. All rights reserved. Rev.: 32187B_AVR UC3C_E_US-0912

Atmel®, Atmel logo and combinations thereof, and others are registered trademarks or trademarks of Atmel Corporation or its subsidiaries. Other terms and product names may be trademarks of others.

Disclaimer: The information in this document is provided in connection with Atmel products. No license, express or implied, by estoppel or otherwise, to any intellectual property right is granted by this document or in connection with the sale of Atmel products. EXCEPT AS SET FORTH IN THE ATMEL TERMS AND CONDITIONS OF SALES LOCATED ON THE ATMEL WEBSITE, ATMEL ASSUMES NO LIABILITY WHATSOEVER AND DISCLAIMS ANY EXPRESS, IMPLIED OR STATUTORY WARRANTY RELATING TO ITS PRODUCTS INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR NON-INFRINGEMENT. IN NO EVENT SHALL ATMEL BE LIABLE FOR ANY DIRECT, INDIRECT, CONSEQUENTIAL, PUNITIVE, SPECIAL OR INCIDENTAL DAMAGES (INCLUDING, WITHOUT LIMITATION, DAMAGES FOR LOSS AND PROFITS, BUSINESS INTERRUPTION, OR LOSS OF INFORMATION) ARISING OUT OF THE USE OR INABILITY TO USE THIS DOCUMENT, EVEN IF ATMEL HAS BEEN ADVISED OF THE POSSIBILITY OF SUCH DAMAGES. Atmel makes no representations or warranties with respect to the accuracy or completeness of the contents of this document and reserves the right to make changes to specifications and products descriptions at any time without notice. Atmel does not make any commitment to update the information contained herein. Unless specifically provided otherwise, Atmel products are not suitable for, and shall not be used in, automotive applications. Atmel products are not intended, authorized, or warranted for use as components in applications intended to support or sustain life.