









- NOTES
- PLEASE SEE SHEET 2 FOR CURRENTLY CONFIGURED PART NUMBERS. FOR SPECIFIC PART NUMBERS PLEASE CONTACT SALES OR CONSULT THE INTELLIGENT PART NUMBERS IN THE TABLE ATTACHED.
 - EARTH POSITION SHOWN, H6.
 - FOR PACKAGING SEE PACKAGING SPEC PK 121065-S19
 - PRODUCT SPEC: SEE PS-121201-001

LAST INSPECTION NUMBER 2



ITEM	DESCRIPTION
1	SCREW
2	COVER ASSEMBLY
3	PCB
4	INSERT ASSEMBLY
5	GASKET

S19207TA022**

SERIES
S19= INTERNAL THREAD FORM C MICRO
POLES
2= 2 POLE & 3= 3 POLE
THREAD
07= PG7, M2= M12x1.5
MATERIAL AND HOUSING COLOUR
G= PA6 GRAY, N= PA6 BLACK, W= PA6 BLACK V0,
T= PA12 TRANSPARENT, B= PA6 WHITE
CIRCUIT
SEE DETAILS IN CATALOGUE
VOLTAGE
SEE DETAILS IN CATALOGUE
SCREW AND GASKET
1= NBR PROFILE GASKET & SCREW
2= NBR FLAT GASKET & SCREW
3= WHITE SILICON PROFILE GASKET & SCREW
4= WHITE SILICON FLAT GASKET & SCREW
A= NBR PROFILE GASKET & SCREW +2mm
B= NBR FLAT GASKET & SCREW +2mm
NON STANDARD COMPONENTS
14= PACKED IN NEUTRAL BAG
5N= PACKED IN BOXES OF 200

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																								
FUNCTIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: REMOVED OBSOLETE PART NUMBERS AS PER PCN#515767				molex															
	mm		2:1																					
	GENERAL TOLERANCES (UNLESS SPECIFIED)																							
	ANGULAR TOL		± 2.0 °		EC NO: 806185 DRWN: VISHAH2 2024/11/25 CHK'D: GGA 2024/12/16 APPR: GGA 2024/12/16				S19 SERIES INTERNAL THREAD															
	4 PLACES		±																					
	3 PLACES		±																					
	2 PLACES		± 0.1																					
	1 PLACE		± 0.2																					
	DIVISIONAL SYMBOLS	0 PLACES		±		INITIAL REVISION: DRWN: JOCONNOR 2011/05/18 APPR: EFOLAN 2011/06/07				PRODUCT CUSTOMER DRAWING														
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION										DRAWING		SERIES		DOCUMENT NUMBER		DOC TYPE		DOC PART		REVISION
				A2-SIZE										121064		SD-121064-003		PSD		001		E1		
																SEE SHEET 2		GENERAL MARKET		1 OF 2				

