

# MIL-DTL-83513/05 Micro-D Jackscrew Kits


















Misc. Backshells  
and Accessories



**Order One Kit Per Connector.** Jackpost kits contain two posts, two hex nuts and 2 lockwashers. Jackscrew kits contain 2 screws and 2 e-rings. Packaged one kit (two screws or posts) per bag.

**Mil Spec Hardware Kits** feature 300 series stainless steel.

| MIL SPEC JACKSCREW KITS                                                                                                       |                                                           |                      |                     |                                                                                      |
|-------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------|----------------------|---------------------|--------------------------------------------------------------------------------------|
| Configuration                                                                                                                 | Connector Size, Thread Size                               | Mil Spec Part Number | Glenair Part Number | Dimensions                                                                           |
| <br><b>Jackpost</b>                          | Sizes 9 to 69 Contacts. Mil Spec Size A to G #2-56 UNC    | M83513/05-07         | 080-00-00-100       |    |
|                                                                                                                               | Size 100 Only Mil Spec Size H #4-40 UNC                   | M83513/05-17         | 080-00-00-101       |    |
| <br><b>Hex Head Jackscrew Low Profile</b>   | Sizes 9 to 69 Contacts. Mil Spec Size A to G #2-56 UNC-2A | M83513/05-02         | 080-00-00-502       |    |
|                                                                                                                               | Size 100 Only Mil Spec Size H #4-40 UNC-2A                | M83513/05-12         | 080-00-00-512       |  |
| <br><b>Slot Head Jackscrew Low Profile</b> | Sizes 9 to 69 Contacts. Mil Spec Size A to G #2-56 UNC-2A | M83513/05-05         | 080-00-00-505       |  |
|                                                                                                                               | Size 100 Only Mil Spec Size H #4-40 UNC-2A                | M83513/05-15         | 080-00-00-515       |  |
| <br><b>Hex Head Jackscrew Extended</b>     | Sizes 9 to 69 Contacts. Mil Spec Size A to G #2-56 UNC-2A | M83513/05-03         | 080-00-00-503       |  |
|                                                                                                                               | Size 100 Only Mil Spec Size H #4-40 UNC-2A                | M83513/05-13         | 080-00-00-513       |  |
| <br><b>Slot Head Jackscrew Extended</b>    | Sizes 9 to 69 Contacts. Mil Spec Size A to G #2-56 UNC-2A | M83513/05-06         | 080-00-00-506       |  |
|                                                                                                                               | Size 100 Only Mil Spec Size H #4-40 UNC-2A                | M83513/05-16         | 080-00-00-516       |  |

Dimensions in inches (millimeters) and are subject to change without notice.

© 2013 Glenair, Inc.

U.S. CAGE Code 06324

Printed in U.S.A.

GLENAIR, INC. • 1211 AIR WAY • GLENDALE, CA 91201-2497 • 818-247-6000 • FAX 818-500-9912  
www.glenair.com G-15 E-Mail: sales@glenair.com

G