

## M23 17 Male -soldered contact



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                               |
|--------------------|-------------------------------------------------------------------------------|
| Part number        | 09 15 117 2603                                                                |
| Specification      | M23 17 Male -soldered contact                                                 |
| HARTING eCatalogue | <a href="https://harting.com/09151172603">https://harting.com/09151172603</a> |

### Identification

|                |                         |
|----------------|-------------------------|
| Category       | Inserts                 |
| Series         | Circular connectors M23 |
| Identification | Signal                  |
| Element        | Inserts                 |

### Version

|                    |                                                                                        |
|--------------------|----------------------------------------------------------------------------------------|
| Termination method | PCB solder termination                                                                 |
| Gender             | Male                                                                                   |
| Number of contacts | 17                                                                                     |
| Details            | Suitable for bulkhead mounted housings 09 15 100 0301, 0302, 0305, 0306 and 0307 only! |

### Technical characteristics

|                       |                 |
|-----------------------|-----------------|
| Rated current         | 8 A             |
| Rated voltage         | 160 V           |
| Rated impulse voltage | 1.5 kV          |
| Pollution degree      | 3               |
| Insulation resistance | $>10^6 \Omega$  |
| Limiting temperature  | -40 ... +125 °C |
| Mating cycles         | $\geq 500$      |

### Material properties

|                   |                |
|-------------------|----------------|
| Material (insert) | Polyamide (PA) |
|-------------------|----------------|



**Pushing Performance**  
Since 1945

## Material properties

|                                           |                                                        |
|-------------------------------------------|--------------------------------------------------------|
| Colour (insert)                           | White                                                  |
| Material (contacts)                       | Copper alloy                                           |
| Surface (contacts)                        | Gold plated                                            |
| Material flammability class acc. to UL 94 | V-0                                                    |
| RoHS                                      | compliant with exemption                               |
| RoHS exemptions                           | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                                | compliant with exemption                               |
| China RoHS                                | 50                                                     |
| REACH Annex XVII substances               | Not contained                                          |
| REACH ANNEX XIV substances                | Not contained                                          |
| REACH SVHC substances                     | Yes                                                    |
| REACH SVHC substances                     | Lead                                                   |
| ECHA SCIP number                          | 052d6da0-30ef-44e8-bbe4-e75780521d22                   |
| California Proposition 65 substances      | Yes                                                    |
| California Proposition 65 substances      | Lead                                                   |

## Specifications and approvals

|          |                       |
|----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
|----------|-----------------------|

## Commercial data

|                                |                                                 |
|--------------------------------|-------------------------------------------------|
| Packaging size                 | 5                                               |
| Net weight                     | 12.2 g                                          |
| Country of origin              | Germany                                         |
| European customs tariff number | 85366990                                        |
| GTIN                           | 5713140187320                                   |
| ETIM                           | EC003557                                        |
| eCl@ss                         | 27440223 Contact insert for circular connectors |