

# CF CRIMPHANDY 1,0 SET - Tool set

1003671

<https://www.phoenixcontact.com/us/products/1003671>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Set consists of: Crimphandy, including battery, charger, cable cutter, 2x waste guide plate, service tool, ferrule strips, robust case, CRIMPHANDY CUTTER, and a tool case



## Product description

Set consists of: Crimphandy 1.0 mm<sup>2</sup>, including battery, charger, CUTFOX 12 cable cutter, waste guide plate 2x, service tool for troubleshooting, and a 1.0 mm<sup>2</sup> ferrule strip, packed in a robust case. A CRIMPHANDY CUTTER, 1.0 mm<sup>2</sup> taped ferrules, 100 strips, each with 50 ferrules per strip, and a tool kit are also provided.

## Your advantages

- Consistently optimum results thanks to automatic monitoring functions
- Unlimited mobile use thanks to battery operation and magazine
- The product innovation for switchgear manufacturing: the Crimphandy. You can strip and crimp your conductors in under two seconds using this portable handheld device. This represents a time saving of 75%.

## Commercial data

Item number	1003671
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	BH3521
GTIN	4055626472027
Weight per piece (including packing)	2,170 g
Weight per piece (excluding packing)	2,170 g
Country of origin	DE

# CF CRIMPHANDY 1,0 SET - Tool set

1003671

<https://www.phoenixcontact.com/us/products/1003671>



Set consists of

CF CRIMPHANDY CUTTER - Accessories for tools/automatic devices

1212520

<https://www.phoenixcontact.com/us/products/1212520>

Cutting unit, for CF CRIMPHANDY, for stranded copper wires from  $0.5 \text{ mm}^2$  ...  $1.5 \text{ mm}^2$ , incl. receptacle tray



---

TOOL-ZIPCASE EMPTY - Toolbag, unequipped

1005050

<https://www.phoenixcontact.com/us/products/1005050>

Tool box, unequipped



# CF CRIMPHANDY 1,0 SET - Tool set

1003671

<https://www.phoenixcontact.com/us/products/1003671>



## Technical data

### Product properties

Product type	Tool set
--------------	----------

### Electrical properties

Frequency range	60 Hz
Power consumption	20 W

### Supply

Supply voltage range	7.4 V DC
----------------------	----------

### Connection data

Stripping length	10.8 mm
Conductor cross-section flexible	1 mm <sup>2</sup> ... 1 mm <sup>2</sup>

### Dimensions

Width	43 mm
Height	70 mm
Length	205 mm

# CF CRIMPHANDY 1,0 SET - Tool set

1003671

<https://www.phoenixcontact.com/us/products/1003671>



## Classifications

### ECLASS

ECLASS-13.0	17130101
ECLASS-15.0	17130101

### ETIM

ETIM 9.0	EC002778
----------	----------

### UNSPSC

UNSPSC 21.0	27111500
-------------	----------

# CF CRIMPHANDY 1,0 SET - Tool set

1003671

<https://www.phoenixcontact.com/us/products/1003671>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-25
An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.	

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	47c10d16-65d8-47ed-989d-d5cc80984d44

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

### Phoenix Contact USA

586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)