

ESL STICK USB A - Software dongle



1080084

<https://www.phoenixcontact.com/us/products/1080084>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

CmDongle for saving licenses for various software products



Product description

Up to 2000 licenses with different license models for various software tools can be stored on the license dongle. Licenses can be used flexibly by moving the dongle from one computer to another. Use of a license dongle is recommended when using virtual machines. This means that licenses can still be used after virtual machines are copied or even if settings are changed on the virtual machine. Using the “Activation Wizard” software tool, activate and deactivate licenses on the license dongle. Or use the “Activation Wizard” to migrate licenses from a PC hard drive to a license dongle (or vice versa), for example. No additional drivers are required to operate the dongle. After it is connected to a computer, it can immediately be used without administrator rights.

Commercial data

Item number	1080084
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR13
Product key	DRDBAZ
GTIN	4055626801926
Weight per piece (including packing)	5.9 g
Weight per piece (excluding packing)	5.3 g
Customs tariff number	84733020
Country of origin	DE

ESL STICK USB A - Software dongle

1080084

<https://www.phoenixcontact.com/us/products/1080084>



Technical data

Notes

Note on application

Note on application

Only for industrial use

Product properties

Product type

Storage medium

Application

Storage of licenses

System properties

License information

Type of license

Activation

Electrical properties

Supply

Supply voltage

5 V (Bus supply, < 20 mA)

Dimensions

External dimensions

Width / Height / Depth

12.1 mm / 4.5 mm / 22 mm

Material specifications

Material

Stainless steel

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)

0 °C ... 70 °C (non-condensing)

ESL STICK USB A - Software dongle



1080084

<https://www.phoenixcontact.com/us/products/1080084>

Classifications

ECLASS

ECLASS-13.0	19159090
-------------	----------

ETIM

ETIM 9.0	EC001068
----------	----------

UNSPSC

UNSPSC 21.0	43202000
-------------	----------

ESL STICK USB A - Software dongle



1080084
<https://www.phoenixcontact.com/us/products/1080084>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	Diboron trioxide(CAS: 1303-86-2)
SCIP	8136ceb2-740e-41b1-acec-c92f1dc6eba0

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com