

CF 500/DIE AI-TWIN 10 - Crimp insert



1212262

<https://www.phoenixcontact.com/us/products/1212262>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die for CF 500 automatic crimping device, for TWIN ferrules (AI-TWIN...) 2 x 4 mm², 2 x 6 mm², and 2 x 10 mm²

Commercial data

Item number	1212262
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH32
Product key	BH323Z
GTIN	4046356449861
Weight per piece (including packing)	68.4 g
Weight per piece (excluding packing)	68.4 g
Customs tariff number	84799070
Country of origin	DE

CF 500/DIE AI-TWIN 10 - Crimp insert



1212262

<https://www.phoenixcontact.com/us/products/1212262>

Technical data

Product properties

Product type	Die
Compression	WM crimp
Max. cross section	4 mm ²
Max. cross section	6 mm ²
Max. cross section	10 mm ²

Connection data

Conductor connection

Cross section range, metric	4 mm ² ... 10 mm ²
-----------------------------	--

Cable/line

External cable diameter	2.4 mm ... 3.7 mm
-------------------------	-------------------

CF 500/DIE AI-TWIN 10 - Crimp insert

1212262

<https://www.phoenixcontact.com/us/products/1212262>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212262>



EAC

Approval ID: RU C-DE.AI30.B.01549

CF 500/DIE AI-TWIN 10 - Crimp insert



1212262

<https://www.phoenixcontact.com/us/products/1212262>

Classifications

ECLASS

ECLASS-13.0	17130192
ECLASS-15.0	17130192

ETIM

ETIM 9.0	EC002778
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CF 500/DIE AI-TWIN 10 - Crimp insert



1212262

<https://www.phoenixcontact.com/us/products/1212262>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com