

CRIMPFOX-RCT 70-1 - Crimping pliers



1212732

<https://www.phoenixcontact.com/us/products/1212732>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Crimping pliers, for uninsulated tube lugs, 10 - 70 mm², indent crimp

Your advantages

- Unlockable pressure lock
- Ergonomically designed handles ensure an optimum grip and help avoid fatigue when working
- Crimping pliers for uninsulated tube lugs
- Compact and lightweight design

Commercial data

Item number	1212732
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3133
GTIN	4046356857918
Weight per piece (including packing)	3,073.3 g
Weight per piece (excluding packing)	3,073.3 g
Customs tariff number	82032000
Country of origin	SE

CRIMPFOX-RCT 70-1 - Crimping pliers



1212732

<https://www.phoenixcontact.com/us/products/1212732>

Technical data

Notes

Environmental Product Compliance

California Proposition 65

Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Crimping tool
Compression	Indent crimp
Product property	Asymmetrical crimp inserts for tubular cable lugs (KSF, KRF, KSD, KRD)
	High gear ratio
	Two-hand operation
	With pressure lock

Crimping position 1

Max. cross section	10 mm ²
AWG max	8

Crimping position 2

Max. cross section	16 mm ²
AWG max	6

Crimping position 3

Max. cross section	25 mm ²
AWG max	3

Crimping position 4

Max. cross section	35 mm ²
AWG max	2

Crimping position 5

Max. cross section	50 mm ²
AWG max	0

Crimping position 6

Max. cross section	70 mm ²
AWG max	00

Connection data

Conductor connection

Cross section range, metric	10 mm ² ... 70 mm ²
-----------------------------	---

Dimensions

Width	44 mm
-------	-------

CRIMPFOX-RCT 70-1 - Crimping pliers



1212732

<https://www.phoenixcontact.com/us/products/1212732>

Height	80 mm
Length	492 mm

Material specifications

Color	black
-------	-------

CRIMPFOX-RCT 70-1 - Crimping pliers



1212732

<https://www.phoenixcontact.com/us/products/1212732>

Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212732>



EAC

Approval ID: RU x-DE.xx08.B.02974

CRIMPFOX-RCT 70-1 - Crimping pliers



1212732

<https://www.phoenixcontact.com/us/products/1212732>

Classifications

ECLASS

ECLASS-13.0	21043811
ECLASS-15.0	21043811

ETIM

ETIM 9.0	EC000168
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CRIMPFOX-RCT 70-1 - Crimping pliers



1212732

<https://www.phoenixcontact.com/us/products/1212732>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
---	---

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com