

THERMOMARK E.CUTTER - Cutter



1234241

<https://www.phoenixcontact.com/us/products/1234241>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cutter for marking materials in continuous format for cutting custom lengths



Product description

Using the cutter, marking materials in continuous format are cut to the desired length, thus creating individual markers. All labels and shrink sleeve versions in continuous format can be processed. The THERMOMARK E.CUTTER cutter can be used with all THERMOMARK E SERIES roll printers and with the THERMOMARK ROLLMASTER 300 / 600.

For a detailed list of all compatible marking systems, go to "Technical data".

Your advantages

- Maximum flexibility: creation of custom individual markers from continuous materials
- Variable lengths can be cut between 10 mm/0.39" ... 2000 mm/78.74"
- Quick and easy mounting of the cutter on the printer
- The cutter can be moved out of the way for convenient material change

Commercial data

Item number	1234241
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG03
Product key	BG122Z
GTIN	4063151337056
Weight per piece (including packing)	1,442 g
Weight per piece (excluding packing)	961.8 g
Customs tariff number	84439990
Country of origin	DE

THERMOMARK E.CUTTER - Cutter



1234241

<https://www.phoenixcontact.com/us/products/1234241>

Technical data

Product properties

Product type	Printing system accessories
--------------	-----------------------------

Marking

Identification technology	Thermotransfer
---------------------------	----------------

THERMOMARK E.CUTTER - Cutter



1234241

<https://www.phoenixcontact.com/us/products/1234241>

Classifications

ECLASS

ECLASS-13.0	19140620
ECLASS-15.0	19140620

ETIM

ETIM 9.0	EC001675
----------	----------

UNSPSC

UNSPSC 21.0	43211600
-------------	----------

THERMOMARK E.CUTTER - Cutter



1234241

<https://www.phoenixcontact.com/us/products/1234241>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com