

UM 72-LG 10 - Lateral element



2959366

<https://www.phoenixcontact.com/us/products/2959366>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Profile housing and board base, 10 mm wide module, consisting of two side elements



Commercial data

Item number	2959366
Packing unit	10 pc
Minimum order quantity	10 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDBA
Catalog page	Page 756 (C-1-2013)
GTIN	4017918117603
Weight per piece (including packing)	13.944 g
Weight per piece (excluding packing)	13.76 g
Customs tariff number	39269097
Country of origin	PL

UM 72-LG 10 - Lateral element

2959366

<https://www.phoenixcontact.com/us/products/2959366>




Technical data

Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UM
Product family	UM72
Type	For PCB dimensions: 8 mm x 72 mm
Type	Lateral element

Dimensions

Dimensional drawing	
Width	8 mm
Depth	89.6 mm
Length	72 mm

Material specifications

Color (Housing)	green (RAL 6021)
Flammability rating according to UL 94	V0
Housing material	PA
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-15 °C ... 50 °C
---------------------------------	------------------

UM 72-LG 10 - Lateral element


2959366

<https://www.phoenixcontact.com/us/products/2959366>



Drawings

Dimensional drawing



UM 72-LG 10 - Lateral element

2959366

<https://www.phoenixcontact.com/us/products/2959366>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2959366>



UL Recognized

Approval ID: E240868

UM 72-LG 10 - Lateral element



2959366

<https://www.phoenixcontact.com/us/products/2959366>

Classifications

ECLASS

ECLASS-13.0	27190602
-------------	----------

ETIM

ETIM 9.0	EC002779
----------	----------

UNSPSC

UNSPSC 21.0	31261500
-------------	----------

UM 72-LG 10 - Lateral element



2959366
<https://www.phoenixcontact.com/us/products/2959366>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com