

WP-G BRASS IP40 PG21 - Protective hose screw connection



3241041

<https://www.phoenixcontact.com/us/products/3241041>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable gland made from brass with Pg thread, IP40 protection

Commercial data

Item number	3241041
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF68
Product key	AF7DSA
Catalog page	Page 598 (C-3-2019)
GTIN	4046356711777
Weight per piece (including packing)	74.87 g
Weight per piece (excluding packing)	74.87 g
Customs tariff number	74122000
Country of origin	DE

WP-G BRASS IP40 PG21 - Protective hose screw connection



3241041

<https://www.phoenixcontact.com/us/products/3241041>

Technical data

Product properties

Product type	Protective hose screw connection
Type of the screw connection	Conduit adapter
Type	Outer thread
Cable outlet	straight
Thread type	Pg

Dimensions

Width	39 mm
Height	40 mm
Length	40 mm
Wrench size	34 mm
Wrench size for mounting	34 mm
	36 mm

External dimensions

Outside diameter	27 mm
------------------	-------

Internal dimensions

Internal diameter	20.5 mm
-------------------	---------

Material specifications

Material	Brass, nickel-plated
Material for screw connection	Brass, nickel-plated
Components	halogen-free

Mechanical properties

Mechanical data

Type of the screw connection	Conduit adapter
------------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-40 °C ... 125 °C

WP-G BRASS IP40 PG21 - Protective hose screw connection



3241041

<https://www.phoenixcontact.com/us/products/3241041>

Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3241041>



VDE approval of drawings

WP-G BRASS IP40 PG21 - Protective hose screw connection



3241041
<https://www.phoenixcontact.com/us/products/3241041>

Classifications

ECLASS

ECLASS-13.0	27430310
-------------	----------

ETIM

ETIM 9.0	EC001180
----------	----------

UNSPSC

UNSPSC 21.0	40141700
-------------	----------

WP-G BRASS IP40 PG21 - Protective hose screw connection



3241041

<https://www.phoenixcontact.com/us/products/3241041>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	acf1ff08-949a-4f3e-9b8a-388b8e150d1d

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com