

# ZB 6,LGS:GLEICHE ZAHLEN 44 - Marker for terminal blocks



1051032:0044

<https://www.phoenixcontact.com/us/products/1051032:0044>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, 10-section, horizontally labeled with the identical number: 44, white, for terminal block width: 6.2 mm, mounting type: latching

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1051032:0044  |
| Packing unit                         | 10 pc         |
| Minimum order quantity               | 10 pc         |
| Sales key                            | BG05          |
| Product key                          | BG2122        |
| GTIN                                 | 4017918513078 |
| Weight per piece (including packing) | 1.473 g       |
| Weight per piece (excluding packing) | 1.273 g       |
| Customs tariff number                | 49119900      |
| Country of origin                    | DE            |

# ZB 6,LGS:GLEICHE ZAHLEN 44 - Marker for terminal blocks



1051032:0044

<https://www.phoenixcontact.com/us/products/1051032:0044>

## Technical data

### Product properties

|              |               |
|--------------|---------------|
| Product type | Klemmenmarker |
| Pitch        | 6.2 mm        |

### Marking

|          |    |
|----------|----|
| Printing | 44 |
|----------|----|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

### Material specifications

|                                        |                                |
|----------------------------------------|--------------------------------|
| Color                                  | white (RAL 9010)               |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|                                                     |                                                                                 |
|-----------------------------------------------------|---------------------------------------------------------------------------------|
| Ambient temperature (operation)                     | -40 °C ... 100 °C                                                               |
| Recommended ambient temperature (storage/transport) | 23 °C                                                                           |
| Recommended humidity (storage/transport)            | 50 % (Storage in a dry and dark place in the original packaging is recommended) |
| Shelf life                                          | 2 years                                                                         |

### Dimensions

|        |         |
|--------|---------|
| Width  | 6.15 mm |
| Height | 10.5 mm |
| Depth  | 4.20 mm |
| Pitch  | 6.2 mm  |

#### Text field

|                   |          |
|-------------------|----------|
| Text field width  | 6.15 mm  |
| Text field height | 10.50 mm |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

# ZB 6,LGS:GLEICHE ZAHLEN 44 - Marker for terminal blocks



1051032:0044

<https://www.phoenixcontact.com/us/products/1051032:0044>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281101 |
| ECLASS-15.0 | 27281101 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC000761 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39131500 |
|-------------|----------|

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)