

# CRIMPFOX-C120 AI 120/DIE - Crimp insert



1209910

<https://www.phoenixcontact.com/us/products/1209910>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Die (pair), for CRIMPFOX-C120, for ferrules (DIN 46228) 120 mm<sup>2</sup>, trapezoid crimp

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1209910       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BH31          |
| Product key                          | BH313Z        |
| GTIN                                 | 4046356178723 |
| Weight per piece (including packing) | 181 g         |
| Weight per piece (excluding packing) | 174.2 g       |
| Customs tariff number                | 82079091      |
| Country of origin                    | DE            |

# CRIMPFOX-C120 AI 120/DIE - Crimp insert



1209910

<https://www.phoenixcontact.com/us/products/1209910>

## Technical data

### Product properties

|                |                   |
|----------------|-------------------|
| Product type   | Die               |
| Compression    | Trapezoidal crimp |
| Crimping width | 26.00 mm          |

### Connection data

#### Conductor connection

|                             |                     |
|-----------------------------|---------------------|
| Cross section range, metric | 120 mm <sup>2</sup> |
|-----------------------------|---------------------|

### Material specifications

|       |       |
|-------|-------|
| Color | black |
|-------|-------|

# CRIMPFOX-C120 AI 120/DIE - Crimp insert



1209910

<https://www.phoenixcontact.com/us/products/1209910>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1209910>



**EAC**

Approval ID: RU x-DE.xx08.B.02974

# CRIMPFOX-C120 AI 120/DIE - Crimp insert



1209910

<https://www.phoenixcontact.com/us/products/1209910>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 21043892 |
| ECLASS-15.0 | 21043892 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC011822 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27111500 |
|-------------|----------|

# CRIMPFOX-C120 AI 120/DIE - Crimp insert



1209910  
<https://www.phoenixcontact.com/us/products/1209910>

## Environmental product compliance

|                                         |                                                                                     |
|-----------------------------------------|-------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                     |
| Fulfills EU RoHS substance requirements | Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE |
| EU REACH SVHC                           |                                                                                     |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                          |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)