

EG 22,5-G/ABS BK - PCB header

2709406

<https://www.phoenixcontact.com/us/products/2709406>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Lower housing part, with snap-on foot



Commercial data

Item number	2709406
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	AC11
Product key	ACHCGA
GTIN	4017918857882
Weight per piece (including packing)	36.44 g
Weight per piece (excluding packing)	27.356 g
Customs tariff number	85369010
Country of origin	DE

EG 22,5-G/ABS BK - PCB header

2709406

<https://www.phoenixcontact.com/us/products/2709406>



Technical data

Product properties

Housing type	Component housing
Type	Lower housing parts with test opening with side cover, housing cover necessary to complete the module
Number of positions	8

Dimensions

Dimensional drawing	
Width	22.5 mm
Height NS 35/7,5	107.5 mm
Depth	75 mm
Length	75 mm

Material specifications

Color	black (RAL 9005)
Flammability rating according to UL 94	HB
Housing material	Acryl butadiene styrene (ABS)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

EG 22,5-G/ABS BK - PCB header


2709406


<https://www.phoenixcontact.com/us/products/2709406>



Drawings


Dimensional drawing






Component mounting side, if the double-level upper part is used

Dimensional drawing



valid for PCB 1, see explosion drawing

Dimensional drawing




valid for PCB 7, see explosion drawing

EG 22,5-G/ABS BK - PCB header

2709406

<https://www.phoenixcontact.com/us/products/2709406>




valid for PCB 13

EG 22,5-G/ABS BK - PCB header

2709406

<https://www.phoenixcontact.com/us/products/2709406>



valid for PCB 14

EG 22,5-G/ABS BK - PCB header

2709406

<https://www.phoenixcontact.com/us/products/2709406>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com