

A-INL-M20-P-LG - Counter nut



1414570

<https://www.phoenixcontact.com/us/products/1414570>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M20 x 1.5, color: light gray



Commercial data

Item number	1414570
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4055626029214
Weight per piece (including packing)	2.63 g
Weight per piece (excluding packing)	2.274 g
Customs tariff number	39269097
Country of origin	TR

A-INL-M20-P-LG - Counter nut

1414570


<https://www.phoenixcontact.com/us/products/1414570>

Technical data

Product properties

Product type	Flat nut
Thread type	M20

Dimensions

Dimensional drawing	
Length	6 mm
Diameter	20 mm
Connecting thread diameter	20 mm
Wrench size, counter nut	26 mm
Hexagon angular dimension	28.6 mm
Thread type connection side	M20 x 1.5
Thread pitch	1.5 mm

Material specifications

Material	PA 6.6 GF
----------	-----------

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

A-INL-M20-P-LG - Counter nut


1414570

<https://www.phoenixcontact.com/us/products/1414570>



Drawings

Dimensional drawing



A-INL-M20-P-LG - Counter nut



1414570

<https://www.phoenixcontact.com/us/products/1414570>

Classifications

ECLASS

ECLASS-13.0	27140807
ECLASS-15.0	27140807

ETIM

ETIM 9.0	EC000879
----------	----------

UNSPSC

UNSPSC 21.0	31161700
-------------	----------

A-INL-M20-P-LG - Counter nut



1414570
<https://www.phoenixcontact.com/us/products/1414570>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com