

S-RT 5-T - Switching lock



3049330

<https://www.phoenixcontact.com/us/products/3049330>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Switching lock, depth: 26.5 mm, width: 8.3 mm, height: 15.65 mm, color: white

Commercial data

Item number	3049330
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE49
Product key	BE4ZWX
GTIN	4046356281034
Weight per piece (including packing)	0.815 g
Weight per piece (excluding packing)	0.769 g
Customs tariff number	85369010
Country of origin	CN

S-RT 5-T - Switching lock

3049330

<https://www.phoenixcontact.com/us/products/3049330>



Technical data

Product properties

Product type	Switching lock
--------------	----------------

Dimensions

Width	8.3 mm
Height	15.65 mm
Depth	26.5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V0
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

S-RT 5-T - Switching lock

3049330

<https://www.phoenixcontact.com/us/products/3049330>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27250190

ETIM

ETIM 9.0	EC004591
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

S-RT 5-T - Switching lock

3049330

<https://www.phoenixcontact.com/us/products/3049330>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com