

SB 1/3/5/7-8-T - Bridge bar

3075845

<https://www.phoenixcontact.com/us/products/3075845>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge bar, number of positions: 7, pin assignment: 1, 3, 5, 7, color: orange



Commercial data

Item number	3075845
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4046356910033
Weight per piece (including packing)	17.52 g
Weight per piece (excluding packing)	17.52 g
Customs tariff number	85369095
Country of origin	PL

SB 1/3/5/7-8-T - Bridge bar

3075845

<https://www.phoenixcontact.com/us/products/3075845>



Technical data

Product properties

Product type	Bridge bar
Number of positions	7
Potentials	1

Material specifications

Color	orange (RAL 2003)
Insulating material	PA

Mechanical properties

Technical data

Pin assignment	1, 3, 5, 7
----------------	------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

SB 1/3/5/7-8-T - Bridge bar

3075845

<https://www.phoenixcontact.com/us/products/3075845>



Classifications

ECLASS

ECLASS-13.0	27250303
-------------	----------

ETIM

ETIM 9.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SB 1/3/5/7-8-T - Bridge bar

3075845

<https://www.phoenixcontact.com/us/products/3075845>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com