

BN-ZB 7,5/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060854

<https://www.phoenixcontact.com/us/products/5060854>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker pin Zack strip, Strip, white, unmarked, can be labeled with: CMS-P1-PLOTTER, mounting type: plug in, for terminal block width: 7.5 mm, Number of individual labels: 1000

Commercial data

Item number	5060854
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG05
Product key	BG2112
GTIN	4017918096083
Weight per piece (including packing)	0.37 g
Weight per piece (excluding packing)	0.346 g
Customs tariff number	39269097
Country of origin	DE

BN-ZB 7,5/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060854

<https://www.phoenixcontact.com/us/products/5060854>

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Klemmenmarker
Pitch	7.5 mm

Marking

Number of individual labels	1000
Number of individual labels per row	10
Identification technology	Plotter

Dimensions

Width	6.30 mm
Height	3.97 mm
Depth	5.50 mm
Pitch	7.5 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	plug in
---------------	---------

BN-ZB 7,5/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060854

<https://www.phoenixcontact.com/us/products/5060854>

Classifications

ETIM

ETIM 8.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

BN-ZB 7,5/WH-100:UNBEDRUCKT - Marker pin Zack strip



5060854

<https://www.phoenixcontact.com/us/products/5060854>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.0 Climate Change

CO2e kg	0.004 kg CO2e
---------	---------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com