

ZB 6/GN-100:UNBEDRUCKT - Zack marker strip



5061484

<https://www.phoenixcontact.com/us/products/5061484>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, Strip, green, unmarked, can be labeled with: PLOTMARK, CMS-P1-PLOTTER, mounting type: snap in, for terminal block width: 6.2 mm, Number of individual labels: 1000

Commercial data

Item number	5061484
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG05
Product key	BG2112
GTIN	4017918096434
Weight per piece (including packing)	1.08 g
Weight per piece (excluding packing)	1.03 g
Customs tariff number	39269097
Country of origin	DE

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Klemmenmarker
Pitch	6.2 mm

Marking

Number of individual labels	1000
Number of individual labels per row	10
Number of marker strips	100

Dimensions

Width	6.15 mm
Height	10.50 mm
Depth	4.20 mm
Pitch	6.2 mm

Material specifications

Color	green (RAL 6021)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN 30646
	DIN VDE 0611

Mounting

Mounting type	snap in
---------------	---------

ZB 6/GN-100:UNBEDRUCKT - Zack marker strip



5061484

<https://www.phoenixcontact.com/us/products/5061484>

Classifications

ETIM

ETIM 8.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 6/GN-100:UNBEDRUCKT - Zack marker strip



5061484
<https://www.phoenixcontact.com/us/products/5061484>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com