


ZBF 5,LGS:GERADE ZAHLEN 82-100 - Zack marker strip

0810821:0082
<https://www.phoenixcontact.com/us/products/0810821:0082>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip flat, 10-section, horizontally labeled with the consecutive even numbers: 82 ... 100, white, for terminal block width: 5 mm, mounting type: latching

Commercial data

Item number	0810821:0082
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4017918862268
Weight per piece (including packing)	0.518 g
Weight per piece (excluding packing)	0.518 g
Customs tariff number	49119900
Country of origin	DE

ZBF 5,LGS:GERADE ZAHLEN 82-100 - Zack marker strip



0810821:0082

<https://www.phoenixcontact.com/us/products/0810821:0082>

Technical data

Product properties

Product type	Labeled terminal marker
Pitch	5 mm
Type	flat

Marking

Printing	82 ... 100
----------	------------

Mounting

Mounting type	latching
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Pitch	5 mm
-------	------

Text field

Text field width	5.15 mm
Text field height	5.15 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

0810821:0082
<https://www.phoenixcontact.com/us/products/0810821:0082>

Classifications

ECLASS		
	ECLASS-13.0	27281101
ETIM		
	ETIM 9.0	EC000761
UNSPSC		
	UNSPSC 21.0	39131500

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com