

NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated



1206586

<https://www.phoenixcontact.com/us/products/1206586>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, unperforated, Pack of 25 (50 m), similar to EN 60715, material: Steel, galvanized, Standard profile, color: silver-colored

Commercial data

Item number	1206586
Packing unit	25 m
Minimum order quantity	50 m
Sales key	BE72
Product key	BE7232
Catalog page	Page 531 (C-3-2019)
GTIN	4017918173067
Weight per piece (including packing)	1,350 g
Weight per piece (excluding packing)	1,350 g
Customs tariff number	72166190
Country of origin	DE

NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated




1206586
<https://www.phoenixcontact.com/us/products/1206586>

Technical data

Product properties

Product type	DIN rail
--------------	----------

Dimensions

Dimensional drawing	
Width	35 mm
Depth	15 mm
Length	2000 mm

Material specifications

Color	silver-colored
Material	Steel
Coating	galvanized

Standards and regulations

Connection in acc. with standard	IEC / EN
Tests	similar to EN 60715

NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated





1206586

<https://www.phoenixcontact.com/us/products/1206586>

Drawings

Dimensional drawing



NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated



1206586
<https://www.phoenixcontact.com/us/products/1206586>

Classifications

ECLASS

ECLASS-13.0	27400602
-------------	----------

ETIM

ETIM 9.0	EC001285
----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

NS 35/15 ZN UNPERF 2000MM - DIN rail, unperforated



1206586

<https://www.phoenixcontact.com/us/products/1206586>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com