

KSS 6 - Short-circuit connector



0301547

<https://www.phoenixcontact.com/us/products/0301547>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Short-circuit connector, pitch: 6 mm, number of positions: 2, color: black

Commercial data

Item number	0301547
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE19
Product key	BE1Z3X
GTIN	4017918000257
Weight per piece (including packing)	3.725 g
Weight per piece (excluding packing)	3.725 g
Customs tariff number	85366990
Country of origin	PL

KSS 6 - Short-circuit connector



0301547

<https://www.phoenixcontact.com/us/products/0301547>

Technical data

Product properties

Product type	Short-circuit connector
Number of positions	2
Pitch	6 mm

Dimensions

Pitch	6 mm
-------	------

Material specifications

Color	black (RAL 9005)
Material	Copper
Flammability rating according to UL 94	V2
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Mounting

Mounting type	Plug-in mounting
---------------	------------------

KSS 6 - Short-circuit connector



0301547

<https://www.phoenixcontact.com/us/products/0301547>

Classifications

ECLASS

ECLASS-13.0	27250303
-------------	----------

ETIM

ETIM 9.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

KSS 6 - Short-circuit connector



0301547

<https://www.phoenixcontact.com/us/products/0301547>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com