

CEC PTPOWER 95/185 - Cover



1056087

<https://www.phoenixcontact.com/us/products/1056087>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cover, yellow, labeled: Lightning flash, mounting type: plug in

Your advantages

- Mains terminal blocks are reliably covered and marked using warning labels
- Accidental actuation of the terminal points is therefore prevented

Commercial data

Item number	1056087
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE22
Product key	BE2ZWX
GTIN	4055626694344
Weight per piece (including packing)	7.38 g
Weight per piece (excluding packing)	7 g
Customs tariff number	85369010
Country of origin	TR

Technical data

Product properties

Product type	Warning label printed
Type	Closed housing

Marking

Printing	Lightning flash
----------	-----------------

Dimensions

Width	24.4 mm
Height	56.4 mm
Depth	56.4 mm

Material specifications

Color	yellow (RAL 1018)
Material	PA
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	plug in
---------------	---------

CEC PTPOWER 95/185 - Cover



1056087

<https://www.phoenixcontact.com/us/products/1056087>

Classifications

ECLASS

ECLASS-13.0	27281107
-------------	----------

ETIM

ETIM 9.0	EC001777
----------	----------

UNSPSC

UNSPSC 21.0	55121700
-------------	----------

CEC PTPOWER 95/185 - Cover

1056087

<https://www.phoenixcontact.com/us/products/1056087>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com