

NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail,
unperforated

0801762
<https://www.phoenixcontact.com/pc/products/0801762>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



DIN rail, unperforated, Pack of 10 (20 m), acc. to EN 60715, material: Copper, uncoated, Standard profile, color: copper-colored

Commercial data

Item number	0801762
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BE7236
GTIN	4017918006693
Weight per piece (including packing)	800.1 g
Weight per piece (excluding packing)	800.1 g
Customs tariff number	74072190
Country of origin	DE

NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail,
unperforated


0801762
<https://www.phoenixcontact.com/pc/products/0801762>

Technical data

Product properties

Product type	DIN rail
--------------	----------

Dimensions

Dimensional drawing	
Width	35 mm
Depth	7.5 mm
Length	2000 mm
Drill hole spacing	0 mm

Material specifications

Color	copper color
Material	Copper
Coating	uncoated

Standards and regulations

Connection in acc. with standard	IEC / EN
Tests	acc. to EN 60715

NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated





0801762

<https://www.phoenixcontact.com/pc/products/0801762>

Drawings

Dimensional drawing



0801762
<https://www.phoenixcontact.com/pc/products/0801762>

Classifications

ECLASS		
ECLASS-13.0		27400602
ETIM		
ETIM 9.0		EC001285
UNSPSC		
UNSPSC 21.0		39121700

NS 35/ 7,5 CU UNPERF 2000MM-VPE 10 - DIN rail, unperforated



0801762

<https://www.phoenixcontact.com/pc/products/0801762>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstraße 8
D-32825 Blomberg
+49 (0) 5235-3 00
info@phoenixcontact.com