

TS-PTVME 6/S - Insulation plate



1193381

<https://www.phoenixcontact.com/us/products/1193381>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insulation plate, depth: 51.5 mm, width: 0.8 mm, height: 82 mm, color: gray



Commercial data

Item number	1193381
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BE29
Product key	BE2Z1X
GTIN	4063151246464
Weight per piece (including packing)	3.67 g
Weight per piece (excluding packing)	3.584 g
Customs tariff number	85389099
Country of origin	CN

TS-PTVME 6/S - Insulation plate



1193381

<https://www.phoenixcontact.com/us/products/1193381>

Technical data

Product properties

Product type	Partition plate
--------------	-----------------

Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

Dimensions

Width	0.8 mm
Height	82 mm
Depth	51.5 mm

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

TS-PTVME 6/S - Insulation plate



1193381

<https://www.phoenixcontact.com/us/products/1193381>

Classifications

ECLASS

ECLASS-13.0	27250301
-------------	----------

ETIM

ETIM 9.0	EC000886
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

TS-PTVME 6/S - Insulation plate



1193381
<https://www.phoenixcontact.com/us/products/1193381>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com