

# ZBF 8 CUS - Zack Marker strip, flat



0825030

<https://www.phoenixcontact.com/us/products/0825030>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack Marker strip, flat, can be ordered: Strip, white, labeled according to customer specifications, mounting type: snap into flat marker groove, for terminal block width: 8 mm, Number of individual labels: 10, text field height: 8.15 mm, text field width: 5.15 mm

## Your advantages

- The ZBF zack marker strip system with flat marker groove is a marking solution for modular terminal blocks and electronics modules
- Other pitches available on request
- Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- The multi-section marking strips are easy to fit and can be easily separated if required

## Commercial data

Item number	0825030
Packing unit	1 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8112
GTIN	4046356357630
Weight per piece (including packing)	0.713 g
Weight per piece (excluding packing)	0.71 g
Customs tariff number	49119900
Country of origin	DE

# ZBF 8 CUS - Zack Marker strip, flat



0825030

<https://www.phoenixcontact.com/us/products/0825030>

## Technical data

### Product properties

Product type	Labeled terminal marker
Pitch	8 mm
Type	flat

### Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	1

### Mounting

Mounting type	snap into flat marker groove
---------------	------------------------------

### Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

### Dimensions

Width	8 mm
Pitch	8 mm

#### Text field

Text field width	5.15 mm
Text field height	8.15 mm

### Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------


# ZBF 8 CUS - Zack Marker strip, flat

0825030

<https://www.phoenixcontact.com/us/products/0825030>

## Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

# ZBF 8 CUS - Zack Marker strip, flat



0825030

<https://www.phoenixcontact.com/us/products/0825030>

## Classifications

### ECLASS

ECLASS-13.0	27281101
-------------	----------

### ETIM

ETIM 9.0	EC000761
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# ZBF 8 CUS - Zack Marker strip, flat



0825030  
<https://www.phoenixcontact.com/us/products/0825030>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)