

CUTFOX-SE LM - Diagonal cutter



1212833

<https://www.phoenixcontact.com/us/products/1212833>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Electrician's diagonal cutter, angled design, with stripping and crimp area, size: 180 mm

Your advantages

- Precision cutting edge for soft and hard wire
- Cutting harder materials with minimal effort due to high leverage
- Special tool steel for permanent use
- Can strip (1.5 mm² and 2.5 mm²), crimp (1.5 mm² ... 2.5 mm²), cut brass screws, and bend eyes (diameter: 4, 5, 6 mm)
- Ergonomically shaped two-component handles for fatigue-free and non-slip use

Commercial data

Item number	1212833
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH311S
GTIN	4055626045528
Weight per piece (including packing)	279.9 g
Weight per piece (excluding packing)	275.6 g
Customs tariff number	82032000
Country of origin	DE

CUTFOX-SE LM - Diagonal cutter

1212833

<https://www.phoenixcontact.com/us/products/1212833>



Technical data

Notes

Environmental Product Compliance	
California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration

Product properties

Product type	Cutting tool
Application	Aluminum
	Copper
Product property	Multifunctional cutter
	With stripping, crimping, shearing, and bending area
	25° angled head
	Inductively hardened precision cutting edge
	Ergonomic two-component handle
	Minimum force required
	Mirror-polished, matt chrome-plated surface
	Special tool steel, die-forged and oil-hardened\
	~ 62 HRC

Dimensions

Length	180 mm
--------	--------

Material specifications

Color	multicolored
-------	--------------

Cable/line

External cable diameter	≤ 11.00 mm
	0.2 mm ... 11 mm

CUTFOX-SE LM - Diagonal cutter

1212833

<https://www.phoenixcontact.com/us/products/1212833>



Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1212833>



EAC

Approval ID: RU x-DE.xx08.B.02974

CUTFOX-SE LM - Diagonal cutter



1212833

<https://www.phoenixcontact.com/us/products/1212833>

Classifications

ECLASS

ECLASS-13.0	21043711
-------------	----------

ETIM

ETIM 9.0	EC000165
----------	----------

UNSPSC

UNSPSC 21.0	27111500
-------------	----------

CUTFOX-SE LM - Diagonal cutter



1212833
<https://www.phoenixcontact.com/us/products/1212833>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Not applicable, No electrical and electronic equipment (EEE), cannot be used in EEE
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com