

# THERMOMARK E.CUTTER - Cutter



1234241

<https://www.phoenixcontact.com/us/products/1234241>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cutter for marking materials in continuous format for cutting custom lengths



## Product description

Using the cutter, marking materials in continuous format are cut to the desired length, thus creating individual markers. All labels and shrink sleeve versions in continuous format can be processed. The THERMOMARK E.CUTTER cutter can be used with all THERMOMARK E SERIES roll printers and with the THERMOMARK ROLLMASTER 300 / 600.

For a detailed list of all compatible marking systems, go to "Technical data".

## Your advantages

- Maximum flexibility: creation of custom individual markers from continuous materials
- Variable lengths can be cut between 10 mm/0.39" ... 2000 mm/78.74"
- Quick and easy mounting of the cutter on the printer
- The cutter can be moved out of the way for convenient material change

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1234241       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | BG03          |
| Product key                          | BG122Z        |
| GTIN                                 | 4063151337056 |
| Weight per piece (including packing) | 1,442 g       |
| Weight per piece (excluding packing) | 961.8 g       |
| Customs tariff number                | 84439990      |
| Country of origin                    | DE            |

# THERMOMARK E.CUTTER - Cutter



1234241

<https://www.phoenixcontact.com/us/products/1234241>

## Technical data

### Product properties

|              |                             |
|--------------|-----------------------------|
| Product type | Printing system accessories |
|--------------|-----------------------------|

### Marking

|                           |                            |
|---------------------------|----------------------------|
| Identification technology | Thermal transfer for rolls |
|---------------------------|----------------------------|

# THERMOMARK E.CUTTER - Cutter



1234241

<https://www.phoenixcontact.com/us/products/1234241>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 19140620 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001675 |
|----------|----------|

# THERMOMARK E.CUTTER - Cutter



1234241  
<https://www.phoenixcontact.com/us/products/1234241>

## Environmental product compliance

|                                         |                                                                                                                                                                                                                                   |
|-----------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS                                 |                                                                                                                                                                                                                                   |
| Fulfills EU RoHS substance requirements | Yes                                                                                                                                                                                                                               |
| Exemption                               | 7(c)-I                                                                                                                                                                                                                            |
| China RoHS                              |                                                                                                                                                                                                                                   |
| Environment friendly use period (EFUP)  | EFUP-10                                                                                                                                                                                                                           |
|                                         | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |
| EU REACH SVHC                           |                                                                                                                                                                                                                                   |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt%                                                                                                                                                                                                        |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)