

SEALING PLUG 6X16 RD - Sealing plug



1400254

<https://www.phoenixcontact.com/us/products/1400254>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Sealing plug, color: red

Commercial data

Item number	1400254
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF68
Product key	AF7DZX
GTIN	4046356478694
Weight per piece (including packing)	0.63 g
Weight per piece (excluding packing)	0.63 g
Customs tariff number	39235090
Country of origin	DE

SEALING PLUG 6X16 RD - Sealing plug



1400254

<https://www.phoenixcontact.com/us/products/1400254>

Technical data

Product properties

Product type	Sealing plugs
--------------	---------------

Dimensions

Dimensional drawing	
Width	5.80 mm
Length	16 mm
Diameter	5.8 mm
	5.8 mm

Material specifications

Material	PA
----------	----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 100 °C
---------------------------------	-------------------

Mounting

Assembly note	The head of the sealing plug must still be visible after mounting in the screw connection (see "after mounting" photo).
---------------	-------------------------------------------------------------------------------------------------------------------------

SEALING PLUG 6X16 RD - Sealing plug


1400254

<https://www.phoenixcontact.com/us/products/1400254>



Drawings

Dimensional drawing



Dimensional drawing

SEALING PLUG 6X16 RD - Sealing plug



1400254

<https://www.phoenixcontact.com/us/products/1400254>

Classifications

ECLASS

ECLASS-13.0	23111190
-------------	----------

ETIM

ETIM 9.0	EC000032
----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

SEALING PLUG 6X16 RD - Sealing plug



1400254
<https://www.phoenixcontact.com/us/products/1400254>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com