

CRIMPFOX DUO 10 SET - Tool set



1044971

<https://www.phoenixcontact.com/us/products/1044971>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cutting, stripping, and crimping set, packaged in a tool case, comprising WIREFOX 10, CRIMPFOX DUO 10, AI SORTI BOX RD, AI TWIN SORTI BOX BU, TOOL-KIT STANDARD EMPTY

Product description

Tool set, equipped

Your advantages

- We have put together a number of attractive tool sets for you by selecting products from our comprehensive range of professional tools
- Universal tools sets with WIREFOX 10, CRIMPFOX-DUO tools from TOOL fox
- Ideal for TWIN ferrule
- Rugged and heavy-duty tool bags

Commercial data

Item number	1044971
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH31
Product key	BH3521
GTIN	4055626622859
Weight per piece (including packing)	1,056.1 g
Weight per piece (excluding packing)	1,056.1 g
Customs tariff number	82060000
Country of origin	SE

CRIMPFOX DUO 10 SET - Tool set



1044971

<https://www.phoenixcontact.com/us/products/1044971>

Set consists of

CRIMPFOX DUO 10 - Crimping pliers

1031721

<https://www.phoenixcontact.com/us/products/1031721>



Crimping pliers, contact connection type: Insulated and uninsulated ferrules, standards/specifications: DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F, min. cross section: 0.14 mm², max. cross section: 10 mm², for TWIN ferrules up to 2 x 4 mm², automatic cross section adjustment, rotating die, lateral and frontal insertion, compression: Trapezoidal crimp, weight 305 g, black/green

WIREFOX 10 - Stripping tool

1212150

<https://www.phoenixcontact.com/us/products/1212150>



Stripping tool, for cables and conductors from 0.02 - 10 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

CRIMPFOX DUO 10 SET - Tool set

1044971

<https://www.phoenixcontact.com/us/products/1044971>



AI SORTI BOX RD - Assortment box

3202960

<https://www.phoenixcontact.com/us/products/3202960>



Assortment box, supplied with ferrules according to DIN 46228-4: 1990-09, 50 pcs. of each. AI 0,5-8 WH, AI 2,5-8 BU, 100 pcs. AI 0,75-8 GY, AI 1-8 RD, AI 1,5-8 BK

AI-TWIN SORTI BOX BU - Assortment box

3202986

<https://www.phoenixcontact.com/us/products/3202986>



Assortment box, supplied with TWIN ferrules in accordance with DIN 46228-4, 50 pcs. each AI-TWIN 2x0,5-8 WH, AI-TWIN 2x0,75-8 GY, AI-TWIN 2x1-8 RD, AI-TWIN 2x1,5-8 BK, 25 pcs. AI-TWIN 2x2,5-10 BU

CRIMPFOX DUO 10 SET - Tool set

1044971

<https://www.phoenixcontact.com/us/products/1044971>



TOOL-KIT STANDARD EMPTY - Toolbag, unequipped

1212423

<https://www.phoenixcontact.com/us/products/1212423>



Tool box, unequipped

CRIMPFOX DUO 10 SET - Tool set



1044971

<https://www.phoenixcontact.com/us/products/1044971>

Technical data

Notes

Environmental Product Compliance

California Proposition 65	Further information on California's prop. 65 is available under "Downloads" in the manufacturer's declaration
---------------------------	---

Product properties

Product type	Tool set
Type of packaging	Bag
Compression	Trapezoidal crimp

Electrical properties

Fuse	DIN 46228-1, DIN 46228-4, UL 486F, form A, E, F
------	---

Dimensions

Width	65 mm
Height	315 mm
Length	165 mm

Material specifications

Color	black (RAL 9005)
-------	------------------

CRIMPFOX DUO 10 SET - Tool set



1044971

<https://www.phoenixcontact.com/us/products/1044971>

Classifications

ECLASS

ECLASS-13.0	21045003
-------------	----------

ETIM

ETIM 9.0	EC000149
----------	----------

UNSPSC

UNSPSC 21.0	27113200
-------------	----------

CRIMPFOX DUO 10 SET - Tool set



1044971
<https://www.phoenixcontact.com/us/products/1044971>

Environmental product compliance

China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com