

ZB 6,LGS:GROSSBUCHSTABEN N - Zack marker strip



1051058:N

<https://www.phoenixcontact.com/us/products/1051058:N>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, horizontally labeled with the capital letter: N, white, for terminal block width: 6.2 mm, mounting type: latching

Commercial data

Item number	1051058:N
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4017918532772
Weight per piece (including packing)	1.54 g
Weight per piece (excluding packing)	1.54 g
Customs tariff number	49119900
Country of origin	DE

ZB 6,LGS:GROSSBUCHSTABEN N - Zack marker strip



1051058:N

<https://www.phoenixcontact.com/us/products/1051058:N>

Technical data

Product properties

Product type	Labeled terminal marker
Pitch	6.2 mm
Type	high

Marking

Printing	N
----------	---

Mounting

Mounting type	latching
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Dimensions

Width	6 mm
Pitch	6.2 mm

Text field

Text field width	6.15 mm
Text field height	10.50 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

ZB 6,LGS:GROSSBUCHSTABEN N - Zack marker strip



1051058:N
<https://www.phoenixcontact.com/us/products/1051058:N>

Classifications

ECLASS

ECLASS-13.0	27281101
-------------	----------

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com