

HC-B10-BCSFS-P-BK - Protective cover



1414625

<https://www.phoenixcontact.com/us/products/1414625>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cover B10, for single locking latch, protective cover material: PA, height: 18.5 mm, seal: no

Commercial data

Item number	1414625
Packing unit	1 pc
Sales key	BF66
Product key	AF7AZC
GTIN	4055626030661
Weight per piece (including packing)	26.6 g
Weight per piece (excluding packing)	20.488 g
Customs tariff number	85389099
Country of origin	DE

HC-B10-BCSFS-P-BK - Protective cover

1414625

<https://www.phoenixcontact.com/us/products/1414625>



Technical data


Notes

General	Protective cover for supporting base element with single locking latch
---------	--

Product properties

Product type	Protective cover
Housing type	Protective cover
Type	B10
Seal present	no

Dimensions

Dimensional drawing	
Width	46 mm
Height	18.5 mm
Length	76 mm
Diameter	40 mm

Material specifications

Material Protective cover	PA
Flammability rating according to UL 94	HB
Material, protective cover	PA

Mechanical properties

Mechanical data	
Locking type	Pin

Environmental and real-life conditions

Ambient conditions	
Degree of protection	IP66
Ambient temperature (operation)	-20 °C ... 100 °C

Mounting

Assembly note	Plastic protective cover for short-term protection
---------------	--

HC-B10-BCSFS-P-BK - Protective cover




1414625

<https://www.phoenixcontact.com/us/products/1414625>

Drawings

Dimensional drawing



Dimensional drawing

HC-B10-BCSFS-P-BK - Protective cover



1414625

<https://www.phoenixcontact.com/us/products/1414625>

Classifications

ECLASS

ECLASS-13.0	27440208
-------------	----------

ETIM

ETIM 8.0	EC002314
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-B10-BCSFS-P-BK - Protective cover



1414625

<https://www.phoenixcontact.com/us/products/1414625>

Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com