

SB 10-8-T IP - Bridge bar

3026496

<https://www.phoenixcontact.com/us/products/3026496>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Bridge bar, pitch: 8.2 mm, number of positions: 10, color: orange

Commercial data

Item number	3026496
Packing unit	10 pc
Minimum order quantity	10 pc
Product key	BE1Z2X
GTIN	4055626021256
Weight per piece (including packing)	11.64 g
Weight per piece (excluding packing)	9.99 g
Country of origin	PL

SB 10-8-T IP - Bridge bar



3026496

<https://www.phoenixcontact.com/us/products/3026496>

Technical data

Product properties

Product type	Bridge bar
Number of positions	10
Pitch	8.2 mm
Potentials	1

Dimensions

Width	80.9 mm
Height	15.6 mm
Depth	15.6 mm
Pitch	8.2 mm

Material specifications

Color	orange (RAL 2003)
Material	Copper, tin-plated
Insulating material	PA

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

SB 10-8-T IP - Bridge bar



3026496

<https://www.phoenixcontact.com/us/products/3026496>

Classifications

ECLASS

ECLASS-13.0	27250303
-------------	----------

ETIM

ETIM 9.0	EC000489
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SB 10-8-T IP - Bridge bar



3026496

<https://www.phoenixcontact.com/us/products/3026496>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com