

# STP 4-2-ZB - Marker carriers



3038613

<https://www.phoenixcontact.com/us/products/3038613>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker carriers, snaps into ST 1,5... spring-cage terminal blocks, can be marked with UC-TM 4, UC-TMF 4, UCT-TM 4, UCT-TMF 4, ZB 4, or ZBF 4, gray, unlabeled, mounting type: latching, text field height: 10.5 mm, text field width: 4 mm

## Your advantages

- The marker carriers can, for example, be snapped into the center marking groove of ST spring-cage terminal blocks and double the labeling area

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3038613       |
| Packing unit                         | 100 pc        |
| Minimum order quantity               | 100 pc        |
| Sales key                            | BG12          |
| Product key                          | BG211A        |
| GTIN                                 | 4017918891275 |
| Weight per piece (including packing) | 0.49 g        |
| Weight per piece (excluding packing) | 0.49 g        |
| Customs tariff number                | 39269097      |
| Country of origin                    | PL            |

# STP 4-2-ZB - Marker carriers



3038613

<https://www.phoenixcontact.com/us/products/3038613>

## Technical data

### Product properties

|              |                 |
|--------------|-----------------|
| Product type | Marker carriers |
|--------------|-----------------|

### Dimensions

|        |          |
|--------|----------|
| Width  | 4 mm     |
| Height | 24.9 mm  |
| Depth  | 24.85 mm |

### Text field

|                   |         |
|-------------------|---------|
| Text field width  | 4 mm    |
| Text field height | 10.5 mm |

### Material specifications

|  |                                |
|--|--------------------------------|
| Color                                  | gray (RAL 7042)                |
| Material                               | PA                             |
| Flammability rating according to UL 94 | V2                             |
| Components                             | free from silicone and halogen |

### Environmental and real-life conditions

#### Ambient conditions

|   |                   |
|---|-------------------|
| Ambient temperature (operation)                     | -40 °C ... 100 °C |
| Recommended ambient temperature (storage/transport) | 23 °C             |
| Recommended humidity (storage/transport)            | 50 %              |

### Mounting

|               |          |
|---------------|----------|
| Mounting type | latching |
|---------------|----------|

# STP 4-2-ZB - Marker carriers



3038613

<https://www.phoenixcontact.com/us/products/3038613>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27281105 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002248 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# STP 4-2-ZB - Marker carriers



3038613

<https://www.phoenixcontact.com/us/products/3038613>

## Environmental product compliance

|   |                            |
|---|----------------------------|
| EU RoHS                                 |                            |
| Fulfills EU RoHS substance requirements | Yes, No exemptions         |
| EU REACH SVHC                           |                            |
| REACH candidate substance (CAS No.)     | No substance above 0.1 wt% |

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)