

UW 10-F - Flange cover

3074525

<https://www.phoenixcontact.com/us/products/3074525>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Flange, number of positions: 0, color: gray

Commercial data

Item number	3074525
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	AA08
Product key	AAHZBA
GTIN	4046356421799
Weight per piece (including packing)	3.544 g
Weight per piece (excluding packing)	3.373 g
Customs tariff number	85472000
Country of origin	CN

UW 10-F - Flange cover

3074525

<https://www.phoenixcontact.com/us/products/3074525>



Technical data

Product properties

Product type	Flange
Product family	BF BEFESTIGUNGSFLANSCH
Number of positions	0
Pitch	0 mm

Dimensions

Pitch	-
-------	---

Material specifications

Color (Housing)	gray (RAL 7042)
Insulating material	PA

UW 10-F - Flange cover

3074525

<https://www.phoenixcontact.com/us/products/3074525>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3074525>

 CSA Approval ID: 13631				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	65 A	20 - 6	-
C				
	300 V	65 A	20 - 6	-
D				
	600 V	5 A	20 - 6	-

 cULus Recognized Approval ID: E60425-20100423				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
B				
	300 V	65 A	20 - 6	-
C				
	300 V	65 A	20 - 6	-
D				
	600 V	5 A	20 - 6	-

UW 10-F - Flange cover

3074525

<https://www.phoenixcontact.com/us/products/3074525>



Classifications

ECLASS

ECLASS-13.0	27460405
ECLASS-15.0	27460405

ETIM

ETIM 9.0	EC002943
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

UW 10-F - Flange cover

3074525

<https://www.phoenixcontact.com/us/products/3074525>



Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%
EF3.0 Climate Change	
CO2e kg	0.03 kg CO2e

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com