

# CABLE-25/8/250/RSM/ARADEx - Adapter cable



2981596

<https://www.phoenixcontact.com/us/products/2981596>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cable adapter for PSR over-speed safety relays (PSR-RSM4 and PSR-MM30), 25/8-pos., cable length: 2.5 m, for controller: Aradex



## Your advantages

- D-SUB connection, 25-pos.
- Length of connecting cable to over-speed safety relay: 2.5 m
- Controller type:ARADEx
- Suitable for connection to the existing motor feedback interface of an electrical drive
- Option to connect to safe PSR-RSM4 and PSR-MM30 over-speed safety relays

## Commercial data

Item number	2981596
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNA251
GTIN	4017918996888
Weight per piece (including packing)	180.4 g
Weight per piece (excluding packing)	180.4 g
Country of origin	DE

# CABLE-25/8/250/RSM/ARADEx - Adapter cable



2981596

<https://www.phoenixcontact.com/us/products/2981596>

## Technical data

### Product properties

Product type	Adapter cable
--------------	---------------

### Connection data

#### To the device

Connection method	RJ45
-------------------	------

#### Encoder / PLC

Connection method	D-SUB-25 male/D-SUB-25 female
Number of positions	25

### Material specifications

Conductor material	Bare Cu litz wires
--------------------	--------------------

### Cable/line

Cable length	2.5 m
Cable cross section	0.48 mm <sup>2</sup> (AWG 26)
Conductor material	Bare Cu litz wires
Shielding	Plastic-coated aluminum foil, tinned copper braided shield Soldering on D-SUB housing
Cable resistance	≤ 260 Ω/km

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 60 °C (for fixed installation) 0 °C ... 50 °C (for flexible installation)
Ambient temperature (storage/transport)	-20 °C ... 70 °C

# CABLE-25/8/250/RSM/ARADEx - Adapter cable



2981596

<https://www.phoenixcontact.com/us/products/2981596>

## Classifications

### UNSPSC

UNSPSC 21.0	26121641
-------------	----------

# CABLE-25/8/250/RSM/ARADEx - Adapter cable



2981596

<https://www.phoenixcontact.com/us/products/2981596>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)