

BMKL 18X 6 WH CUS - Label sheet, DIN A4



0824242

<https://www.phoenixcontact.com/us/products/0824242>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Label sheet, DIN A4, can be ordered: in sheets, white, labeled according to customer specifications, mounting type: adhesive, Number of individual labels: 396, text field height: 6 mm, text field width: 18 mm



Your advantages

- These labels have been specially developed for laser printers
- Labeling service: Phoenix Contact can custom-label all BMKL ... markers according to your requirements
- Can be printed on all commercially available laser printers
- The unperforated SK-U... sheets are available for custom label designs

Commercial data

Item number	0824242
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8144
GTIN	4046356351171
Weight per piece (including packing)	10 g
Weight per piece (excluding packing)	9 g
Country of origin	PL

BMKL 18X 6 WH CUS - Label sheet, DIN A4



0824242

<https://www.phoenixcontact.com/us/products/0824242>

Technical data

Product properties

Product type	Gerätemarker
--------------	--------------

Marking

Number of individual labels	396
Number of individual labels per row	9
Identification technology	Office laser printing

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

Color	white (RAL 9010)
Material	Polyester
Base element material	Polyester
Components	Silicone-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 80 °C
---------------------------------	------------------

Dimensions

Width	6.00 mm
Height	18.00 mm
Depth	0.09 mm
Length	6 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

BMKL 18X 6 WH CUS - Label sheet, DIN A4



0824242

<https://www.phoenixcontact.com/us/products/0824242>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

BMKL 18X 6 WH CUS - Label sheet, DIN A4



0824242

<https://www.phoenixcontact.com/us/products/0824242>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com