

ZB 8/BU CUS - Zack marker strip



0824998

<https://www.phoenixcontact.com/us/products/0824998>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Zack marker strip, can be ordered: Strip, blue, labeled according to customer specifications, mounting type: snap into tall marker groove, for terminal block width: 8.2 mm, Number of individual labels: 10

Commercial data

Item number	0824998
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	BG24
Product key	BG8112
GTIN	4046356357470
Weight per piece (including packing)	1.889 g
Weight per piece (excluding packing)	1.889 g
Customs tariff number	49119900
Country of origin	DE

ZB 8/BU CUS - Zack marker strip



0824998

<https://www.phoenixcontact.com/us/products/0824998>

Technical data

Product properties

Product type	Klemmenmarker
Pitch	8.2 mm

Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10

Mounting

Mounting type	snap into tall marker groove
---------------	------------------------------

Material specifications

Color	blue (RAL 5015)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
---------------------------------	-------------------

Dimensions


Width	8.15 mm
Height	10.50 mm
Depth	4.30 mm
Pitch	8.2 mm

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Drawings

Schematic diagram



- ① Horizontal
- ② Vertical

ZB 8/BU CUS - Zack marker strip



0824998

<https://www.phoenixcontact.com/us/products/0824998>

Classifications

ETIM

ETIM 8.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

ZB 8/BU CUS - Zack marker strip



0824998

<https://www.phoenixcontact.com/us/products/0824998>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com