

# PTFIX-NS35 - DIN rail adapter

3274054

<https://www.phoenixcontact.com/us/products/3274054>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

DIN rail adapter, for NS 35 and NS 15 for accommodating 2.5 mm<sup>2</sup>, 4 mm<sup>2</sup>, and 10 mm<sup>2</sup> FIX blocks in vertical direction, color: gray



## Commercial data

Item number	3274054
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	BE09
Product key	BEAZ11
GTIN	4055626377162
Weight per piece (including packing)	4.595 g
Weight per piece (excluding packing)	4.515 g
Customs tariff number	39269097
Country of origin	PL

# PTFIX-NS35 - DIN rail adapter



3274054

<https://www.phoenixcontact.com/us/products/3274054>

## Technical data

### Notes

Assembly note	for NS 35 and NS 15 for accommodating 2.5 mm <sup>2</sup> , 4 mm <sup>2</sup> , and 10 mm <sup>2</sup> FIX blocks in the vertical direction
---------------	---

### Product properties

Product type	Mounting material
--------------	-------------------

### Dimensions

Width	28.6 mm
Height	58.1 mm
Depth	11 mm
Depth on NS 35/7,5	15 mm
Depth on NS 35/15	22.5 mm

### Material specifications

Color	gray (RAL 7042)
Material	PA
Flammability rating according to UL 94	V0

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Mounting

Mounting type	NS 35/7,5
	NS 35/15
	NS 15

# PTFIX-NS35 - DIN rail adapter



3274054

<https://www.phoenixcontact.com/us/products/3274054>

## Classifications

### ECLASS

ECLASS-13.0	27370419
ECLASS-15.0	27370419

### ETIM

ETIM 9.0	EC001024
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# PTFIX-NS35 - DIN rail adapter



3274054

<https://www.phoenixcontact.com/us/products/3274054>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)