

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Pipeline marker, can be ordered: by line, blue, labeled according to customer specifications:  
Oxygen, mounting type: adhesive, diameter: 0 mm



Your advantages

- Group 0 (oxygen)

Commercial data

|                                      |                                |
|--------------------------------------|--------------------------------|
| Item number                          | 1014268                        |
| Packing unit                         | 1 pc                           |
| Minimum order quantity               | 1 pc                           |
| Note                                 | Made to order (non-returnable) |
| Product key                          | BG8151                         |
| GTIN                                 | 4046356784740                  |
| Weight per piece (including packing) | 1.99 g                         |
| Weight per piece (excluding packing) | 1.99 g                         |
| Country of origin                    | PL                             |

# PML-T110 (52X560)R CUS - Pipeline marker



1014268

<https://www.phoenixcontact.com/us/products/1014268>

## Technical data

### Product properties

|                     |                                               |
|---------------------|-----------------------------------------------|
| Product type        | Labeled systems marker                        |
| Area of application | Pipeline identification according to DIN 2403 |
| Type                | Rectangle                                     |

### Marking

|                                     |        |
|-------------------------------------|--------|
| Number of individual labels per row | 1      |
| Printing                            | Oxygen |

### Dimensions

|        |        |
|--------|--------|
| Width  | 560 mm |
| Height | 52 mm  |
| Length | 52 mm  |

### Material specifications

|                |                 |
|----------------|-----------------|
| RoHS compliant | yes             |
| Foil strength  | 50 µm           |
| Adhesive       | Acrylic         |
| Color          | blue (RAL 5015) |
| Material       | Polyester       |

### Environmental and real-life conditions

#### UV resistance

|               |                                |
|---------------|--------------------------------|
| Specification | ISO 4892-2:2013-03 (following) |
| Result        | Test passed                    |
| Test duration | 96 h                           |

#### Ambient conditions

|                                 |                                                                                                         |
|---------------------------------|---------------------------------------------------------------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 150 °C                                                                                       |
| Recommended storage conditions  | 23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended. |
| Shelf life                      | 2 years                                                                                                 |

### Standards and regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Mounting

|               |          |
|---------------|----------|
| Mounting type | adhesive |
|---------------|----------|

# PML-T110 (52X560)R CUS - Pipeline marker



1014268

<https://www.phoenixcontact.com/us/products/1014268>

## Classifications

### ETIM

|          |          |
|----------|----------|
| ETIM 8.0 | EC001777 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 55121700 |
|-------------|----------|

# PML-T110 (52X560)R CUS - Pipeline marker



1014268

<https://www.phoenixcontact.com/us/products/1014268>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)